


Laser Screen 2.4

Designed to amplify the full potential of laser projection by Barco



- **Enhanced appearance**
- **Precision sharpness**
- **Even better uniformity**
- **Both 2D and 3D**
- **Efficient Sustainability**

The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible. The new Barco Laser Screen 2.4 has been designed to complement and enhance Laser Projection by Barco. The laser-matched pair work in harmony to enhance and elevate what's visually possible.

Cinematic brilliance

Elevate your cinematic experience to unprecedented heights with the Barco Laser Screen 2.4. Crafted through years of industry-leading expertise, extensive cinema knowledge, and in-house innovation, this screen is precision designed to amplify the full potential of laser projection in today's cinema landscape.

Laser performance

When you pair the new screen with Laser Projection by Barco, the result is an unparalleled visual performance – that you and your audiences will notice.

The marriage of the best laser projection technology with the Barco Laser Screen 2.4 delivers laser-powered movie experiences at a new level in both 2D and 3D.

Experience

Designed and tested by cinema experts, the new Barco cinema screen will delight moviegoers around the world.

Product specifications**LASER SCREEN 2.4****Ogólne specyfikacje**

| | |
|---------------------------|---|
| Wzmocnienie | 2.4: 23°HGA |
| Stosunek sygnału do szumu | 220+ |
| Perforacja | Micro-perforated (3.5% void) |
| Powierzchnia | Textured PVC with High Gain Coating |
| Szerokość materiału | 54" – 1.4 m |
| Grubość | Approx. 0.0154" – 0.39 mm |
| Waga | Approx. 0.0154" – 0.39 mm |
| Ognioodporność | NFPA-701, M3, BS 5867 Part 2: 2008 Type B, B1 Please contact us for additional certification requirements |
| Krawędzie | PVC grommets every 9 inches center to center Pipe pockets, Velcro, snaps and other edging options available upon request |
| Opakowanie | Rolled on a cardboard tube into a highly resistant carton |
| Okres gwarancji | 24 Months |

Last updated: 17 Oct 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.

www.barco.com

BARCO