

FS40-4K MKII

Rock-solid and powerful 4K LED projector for NVG training



- Extreme detail up to 4K (3840 x 2400) resolution
- Night Vision Goggles stimulation
- True solid-state and ruggedized
- Brighter LEDs with exceptional color fidelity
- 100-0% LED dimming for training at any time
- Barco Pulse software ensures powerful processing and lowest latency

The FS40-4K MKII is the latest in the line of true solid-state simulation-ready projectors from Barco. Combining LED illumination technology with Barco Pulse electronics performance, the FS40 delivers visual excellence and extreme reliability with a low TCO. Designed for simulation applications, the FS40 features both an RGB and a dedicated IR light source, which allows for individual control of visible light and IR intensity to simulate daytime and nighttime training scenarios. Dual iris and optical filters ensure optimal contrast and deeper black levels for best in class image clarity. Designed for the most demanding simulation environments, the FS40 delivers a vision to trust.

Extreme reliability in all situations

Using the latest LED illumination, the FS40 produces high brightness images with optimal clarity and color gamut. The FS40-4K is a native WQXGA resolution projector and uses the performance of Barco Pulse to show images up to 4K resolution (3840 x 2400). Thanks to the Single Step Processing (SSP®) technology in Barco Pulse the FS40 benefits from built-in warp and blend, high resolution images at higher frame rates with lower latency than competing technology.

The Barco FS40 is a true solid-state projector designed for motion platforms with no moving parts. It is rock solid designed for shock and vibration. Its solid magnesium alloy baseplate act as mounting plate. Coupled with an array of mounting points in the front and on the top cabinet, they make this projector solid as rock and perfectly suited for use on motion platforms in any orientation.

Lowest TCO

The FS40 uses a proven DLP® sealed optical engine and the latest solid-state LED illumination. Simulator operators can benefit from reduced Total Cost of Ownership (TCO) with extended maintenance cycles and no lamp changes or color adjustments for up to 50,000hrs. Barco Constant Light Output (CLO) functionality ensures predictability in linear brightness performance over the life of the projector. Additional protection is available when using new intelligent high-efficiency air filters for installations in dusty and harsh environments.

Product specifications**FS40-4K MKII**

General specifications	
Brightness	2,870 Typical ANSI Lumens
Contrast ratio	1800-6000:1
IR for NVG	Yes
Brightness uniformity	90%
Aspect ratio	16:10
Projector type	1DLP RGB LED
Resolution	3,840 x 2,400 (4K) / 2,560 x 1,600 (native)
Lens type	FLD+/FLDX
Optical lens shift	Vertical up to 146%, depending on lens Horizontal up to 70%, depending on lens Motorized zoom and focus (+ lens memory FLDX lenses) Motorized lens shift (with position memory on all lenses)
Color correction	P7 RealColor™
CLO (constant light output)	Yes
Light source	RGB LED
Light source lifetime	Up to 50,000 hours
Sealed DLP™ core	Yes
Orientation	360° rotation, no restrictions
3D	Active stereoscopic 3D
Image processing	Embedded warp & blend engine
Keystone correction	Yes
Inputs	2x DP1.2 2x dual link DVI-I HDBaseT upgradable HDMI 2.0 (HDCP2.2, HDR10) RJ 45 Ethernet RS232 in 2x USB 12v out
Input resolutions	Including and up to: 3,840 x 2,400 @ 60Hz 3,840 x 2,160 @ 60Hz 4,096 x 2,160 @ 60Hz 2,560 x 1,600 @ 120Hz
Input color depth	DVI: Including and up to 2560x1600@60Hz 8 bit RGB and 3840x2400@50Hz 8 bit RGB DisplayPort: Including and up to 2560x1600@120Hz 12 bit RGB and 3840x2400@60Hz 8 bit RGB
Software tools	Projector Toolset
Control	IR, RS232, RJ45
Network connection	IR, RS232, RJ45
Power requirements	100-240V / 50-60Hz
Power consumption	500 W typical, 570 W maximum
BTU per hour	1,707 BTU/h typical, 1,945 BTU/h max
Noise level (typical at 25°C/77°F)	33 dB(A)
Operating temperature	10 -40 °C (sea level)
Storage temperature	-20 to 60 °C
Operating humidity	20 -80% RH
Storage humidity	10 -90% RH
Dimensions (WxLxH)	450 x 457 x 244 mm / 17,7 x 18,0 x 9,6 in
Weight	21,5 kg / 47,4 lbs
Standard accessories	Power cord, wireless remote control
Certifications	CE, FCC Class A and cNus
Warranty	Limited 5 years parts and labor, extendable

Last updated: 29 Jun 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.