


D310



- -

3 to 2 and 2 to 2 Pull Down (patented Motion Picture Processing)-Time Based Correction-Video Equalizing (3-Band)-
Dynamic Image Stabilization-
Digital Brightness/Saturation Control-Scaler/Compressor-
Automatic RGB Matrix Selection-
Analytical Contrast Rendering (Stretch to SubBlack,
Gamma (RGB))-Luminance Tracking-
Dynamic Sample Weight Distribution

一般仕様	
互換性	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43 in Composite, S-VHS, RGB or Component format) -All computer graphics up to SVGA (800 x 600) -All Macintosh computers (640 x 480) -Pannellink loop through data signal
入力	-Two Composite Video inputs on BNC connectors -Two S-video inputs on 4 pin mini-Din connectors -Once Component Video input (R-Y, B-Y, Y, sync) on 4 x BNC connectors -One RGBs or RGsB input on 4 x BNC connectors -One Pannellink input
出力	-Pannellink data output -Long/Short Distance digital link -RGBs or RGsB output on HD15 connector (monitor) -RS 232 loop-through communication port on D9 male & female connectors -RS 485 Phoenix connectors for AX Link

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

