

# Galaxy NW-7 MK I

3D stereo, network-centric, 7,000 lumens, WUXGA, three-chip DLP projector



**Product specificaties****GALAXY NW-7 MK I****General specifications**

|                        |                                                                                                                                                                   |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Lichtuitvoer           | 7,000 lumens                                                                                                                                                      |
| Contrastverhouding     | up to 2,000:1                                                                                                                                                     |
| Resolutie              | WUXGA (1920x1200px)                                                                                                                                               |
| Type chip              | Three-chip DLP                                                                                                                                                    |
| Lamp                   | 1.5 kW xenon lamp                                                                                                                                                 |
| Lampgarantie           | 1000 hrs warranted                                                                                                                                                |
| Gewicht                | 70kg (154.2lbs)                                                                                                                                                   |
| Afmetingen (B x L x H) | 590x913x345mm (23.22x35.94x13.58")                                                                                                                                |
| Lensverschuiving       | Horizontal up to -/+ 65% Vertical up to -/+ 110%                                                                                                                  |
| Standaardingenangen    | 1x 5-BNC (RGBHV, RGBS or RGBsB)<br>1x composite video (BNC)<br>1x S-video (4-pin mini DIN)<br>Twin dual-link DVI<br>3 stereo sync inputs (mini DIN)               |
| Optionele ingangen     | One free layer (see options)                                                                                                                                      |
| Communicatiepoort      | RS232 (on D9)<br>10/100 Mb/s Ethernet (on RJ45)                                                                                                                   |
| Video                  | PAL, SECAM, NTSC video signals in Composite, S-video, component or RGB format<br>All current HDTV standards (720i, 720p, 1080i, 1080p) in component or RGB format |
| Gegevens               | All computer graphics formats up to QXGA @ 120 Hz<br>Analog sources with a pixel clock of up to 270 MHz<br>DVI sources with a pixel clock of up to 270 MHz        |
| Veiligheid             | ETL60950 and EN60950<br>CE compliant<br>CCC compliant                                                                                                             |
| Wisselstroom           | 200-240V                                                                                                                                                          |
| Max. energieverbruik   | 2,800 Watt / 9,560 BTU                                                                                                                                            |

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.

[www.barco.com](http://www.barco.com)**BARCO**