


OverView KVD-5521D

55" ultra narrow bezel (UNB) LCD video wall for entry level and mid-end applications



- 500 Nit brightness, UNB generation
- Superb inter-tile color and brightness
- User-friendly video-wall setup and control interface
- Sense X brightness and color automatic calibration with integrated sensors
- Fan-less solution for noiseless performance
- Reduced energy consumption
- Optional 5-year service packages

Barco's new OverView KVD-5521D is a high-performance, mid-level brightness (500 cd/m² typical) and cost-optimized 55" LCD-panel, dedicated for use in tiled video wall applications. A video wall of the UNB 3.5 mm/0.14" bezel width generation, with great colors and reduced energy consumption compared to previous models, the OverView KVD-5521D provides great value to entry level and mid-end applications.

A perfect image with automatic color and brightness calibration

The OverView KVD-5521D is part of Barco's highly renowned and industry-leading OverView LCD video wall portfolio -which complements the premium Barco UniSee platform. The signature innovative Sense X -Barco's automatic real-time color and brightness calibration system -ensures that the complete wall produces a perfectly balanced image at all times. This avoids the dreaded 'checkerboard' pattern image in video walls. Barco is the only company in the market enabling this type of automatic calibration in real-time based on integrated brightness and color sensors.

Enhanced uptime, reduced power consumption

The use of Barco's Video wall Manager makes it much easier to control the video wall, further improving the user-friendliness.

Compared to the previous model, the KVD-5521D consumes 25% less energy. This helps companies to both reduce costs and achieve their sustainability goals.

Product specificaties**OVERVIEW KVD-5521D**

| Panel | |
|---|---|
| Resolutie | Full HD (1920 x 1080 pixels) |
| Achtergrondverlichting | Direct LED |
| Beeldverhouding | 16:9 |
| Luminantie | 500 cd/m ² (typ.) |
| Contrast | 1200:1 (typ.) |
| Wit punt | Native 10000 K (typ.) |
| Kalibratie | Sense X automatic color and brightness calibration |
| Levensduur van de achtergrondverlichting | 50000 h (typ.) |
| Koeling | Fan-less |
| Schermniveau | 25% |
| Bedrijfstemperatuur | 0 – 40°C |
| Operationele vochtigheid | 20 – 80% non-condensing |
| Opslagtemperatuur | -20 – 60°C |
| Vochtigheid bij opslag | 10 – 80% non condensing |
| Montage | VESA 600 x 400 |
| Power | |
| Ingangsspanning (wisselstroom) | 100 – 240 VAC, 50 – 60 Hz |
| Energieverbruik | 160W (500 Nit Native) |
| Warmteafvoer | 546 BTU/h |
| Dimensions | |
| Afmetingen | 1213 x 683.8 x 122.5 mm 47.77" x 26.94" x 4.83" |
| Actief scherm (diagonaal) | 55" (1397 mm) |
| Actief schermgebied | 1211.3 mm x 682.1 mm 47.62" x 26.79" |
| Gewicht | 27.55 kg 60.74 lbs |
| Totale breedte van omlijsting (twee aangrenzende beeldschermen) | UNB (3.5 mm 0.14") generation; actual width: 3.4 mm 0.13" |
| Connectivity | |
| DisplayPort | 2 DP1.2 inputs (DisplayPort 1.2 cables must be used when the cable length exceeds 3m / 10 ft) 1 DP1.2 output |
| HDMI(TM) | 2 HDMI 2.0 inputs |
| Ethernet-poort | 1 |
| USB | 1 input (only for power) |
| HDCP | Yes (HDCP 2.2) |
| Model | |
| Modelnaam | OverView KVD-5521D |

Laatst bijgewerkt: 30 May 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.