


# Barco UniSee

55" bezel-less tiled LCD video wall platform for high-brightness applications



- **Bezel-less design with NoGap technology, for high-brightness use**
- **Mounting structure with automatic alignment for ensured precision**
- **Sense X automatic and continuous calibration**
- **Modular, future-proof platform**

The award-winning Barco UniSee® platform takes a completely new approach to truly seamless LCD video walls. Redesigning and optimizing every component, Barco UniSee is not only a step forward in terms of image quality, but also in installation precision, ease-of-servicing, and reliability.

### **Bezel-less viewing experience, innovative mounting system**

Barco UniSee's bezel-less design, which makes the inter-tile gap barely noticeable, enables spreading content over multiple tiles without the interruption of a disturbing black border. The revolutionary UniSee Mount uses the power of gravity to perfectly and automatically align panels – and keep them in place over time. What's more, UniSee Mount also eases maintenance efforts, allowing swift undocking of separate panels.

### **Sense X, automatic and continuous calibration for perfect uniformity**

Sense X, the automatic, continuous color and brightness calibration system, ensures that the complete wall gives a perfectly balanced image at all times. What's more, Barco has also re-engineered the design of the panels to counter all possible variations in brightness from the center to the edges.

Setup and maintenance can be performed even faster and more easily using the upgraded Video wall Manager module. A wizard guides you through the complete installation process, and the individual panels are automatically recognized by the software upon introduction. The local dimming feature brings higher contrast, lower radiated heat and reduced power consumption.

### **Offering full system experiences**

Besides its visualization portfolio, Barco offers a full range of content management solutions and services to meet the needs of several applications. In addition, the Barco UniSee platform is surrounded by several ecosystem partners, that offer tailored components to further increase the platform's value. Think of touch overlays for increased interactivity, trim solutions for elegant integration in the environment, mounting solutions to allow free-standing or curved set-ups, etc.

**Product specifications****BARCO UNISEE**

<b>Model</b>	
Model name	Barco UniSee 700
<b>Panel</b>	
LCD technology	IPS
Resolution	Full HD (1920 x 1080)
Backlight	Direct LED
Aspect ratio	16:9
Luminance	700 cd/m <sup>2</sup> (TYPICAL)
Contrast	1100:1 (TYPICAL)
Contrast	1500:1 (TYPICAL*)
White point	native: 10,500 K (TYPICAL)
Screen haze	28%
Calibration	Sense X automatic color and brightness calibration
Bit depth	3 x 10 bits
Backlight lifetime	60,000 h (TYPICAL)
Viewing angle (H, V)	178°   178°
Uniformity	9 points: 98% 13 points: 98% 21 points: 92%
Cooling	Fanless
Operating temperature	0°C - 40°C
Operational humidity	20% - 80% (non-condensing)
Storage temperature	-20°C - 60°C
Storage humidity	10% - 90% (non-condensing)
Response time	< 8 ms
Temperature sensors	Embedded temperature sensors in each panel
Image retention	Advanced algorithms to limit image retention
*Note	*: tested with a 3x3 checkerboard test pattern on a single panel with default factory settings.
<b>Dimensions</b>	
Dimensions	1211.36 x 682.02 x 91.1 mm   47.7" x 26.9" x 3.59" (internal SMPS) 1211.36 x 682.02 x 87.1 mm   47.7" x 26.9" x 3.43" (external SMPS)
Active screen diagonal	55"
Weight	17.3 kg   38.1 lbs (LCD net) 15.0 kg   33.1 lbs (LCM net)
Bezel Width	NA (bezel-less)
<b>Connectivity</b>	
DisplayPort	2 DP1.2 inputs (DisplayPort 1.2 cables must be used when the cable length exceeds 3m / 10 feet) 1 DP1.2 output
HDMI	2 HDMI 2.0 inputs
USB	2 (only for power)
Ethernet port	2
HDCP	Yes (v2.2)
<b>Power</b>	

**Product specifications****BARCO UNISEE**

AC input voltage	100-240 VAC, 50-60 Hz		
Power consumption		Int. power supply	Ext. power supply
	700 nit	241W	227 W
	500 nit	185 W	174 W
	350 nit	139 W	130 W
Heat dissipation	700 nit	822 BTU/h	775 BTU/h
	500 nit	631 BTU/h	594 BTU/h
	350 nit	474 BTU/H	444 BTU/h
EMC	Class A and follows CE, FCC or UL Emission: EN 55032: 2012 EN 61000-3-2: 2014 EN 61000-3-3: 2013 Immunity: EN 55024: 2010		
Product safety	EN 60950-1: 2006 + A11: 2009 + A1: 2010 + A12: 2011 + A2: 2013		
RoHS	EN 50581: 2012		
Components	UNI-0001 / UNI-0002 / UNI-0004 / UNI-0005 & WME110		
Notes	UniSee Mount can support up to 10 rows in lanscape mode and 6 rows in portrait		

Last updated: 12 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.