

BarcoReality 812



Product specifications**BARCOREALITY 812****General specifications**

Contrast	>1000:1 (full white/full black)
Light output	1300 Lumen (at 10 % peak white) 350 Lumen (Economy mode) 410 Lumen (Normal mode) 500 Lumen (Boost mode)
Screen size	Min.: 2.4 m x 1.8 m (7.9' x 5.9') Max.: 7.0 m x 5.25 m (23' x 17.3')

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.