

SP4K-25

23,500 lumens smart cinema projector



23.5K
LUMENS

4K
4096X2160



- Brilliant image
- Ready for tomorrow, today
- Barco EcoPure™
- Fit and forget

SP4K-25 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

Brilliant image

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ includes patented technology to guarantee sharp, consistent image quality over time.

Ready for tomorrow, today

With the SP4K models and their RGB laser lightsource, the Barco Colorgenic™ technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

Barco EcoPure™

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-25 smartly manages its power consumption reaching projector efficiency levels up to 9.5 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-25 seamlessly integrates into your current setup.

Product specificaties**SP4K-25**

| General specifications | |
|---------------------------------------|---|
| Native helderheid | 23,500 lumens (typical) |
| Native contrastverhouding | 2300:1 (typical) up to 3000:1 with HC lens |
| Digital MicroMirror Device™ | 3x 0.98" DC4K |
| Resolutie | native 4K: 4096 x 2160 |
| Kleurenspectrum | DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates) |
| Lichtbron | Laser |
| Primelenzen | With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9 With B-lensholder: 1.01; 1.27; 1.6 – 2.4; 1.9 – 2.6; 2.0 – 2.95; 2.3 – 3.65; 2.8 – 4.7; 3.55 – 6.95 High-brightness and High-contrast B-lenses compatible |
| Langdurige stabiliteit van helderheid | 40,000 hrs @ average usage conditions |
| Behuizing | integrated cooling design and patented sealed optical assembly |
| Afmetingen (B x L x H) | Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches 710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder |
| Gewicht | 105kg / 231.5lbs |
| Voedingsvereisten | single phase or triple phase 200-240V 16A |
| Warmtebelasting (max. vermogen) | 7750 BTU/hr |
| Luchtuitstroom | 400CFM |
| Omgevingstemperatuur | 40°C/104F Max. |
| Omgevingsvochtigheid | 85% RH Max. |
| Mediaserver | Barco Alchemy ICMP-X and other media server brands** supported. |
| Energieverbruik | 2.4kW (3W in Eco mode) |
| Geluidsniveau | 50dB(A) @ 1m and @ 25°C ambient temperature |
| 3D-systemen | Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported. |
| Veiligheidsvereisten | Class 1 risk group 3 |
| Gebruikersinterface | Touch Display and/or web based |
| Laterale lenskleur op beeldrand | With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...) |
| Opmerkingen | **projector configuration with ICP-D; contact Barco service for the list of supported brands |

Laatst bijgewerkt: 09 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.