

Galaxy 4 LL+

Stereo dedicated "long-life" projector with lamp life up to 2000 hours



技术规格**GALAXY 4 LL+**

一般规格	
光输出	4000 ANSI lumens
分辨率	1400 x 1050 (SXGA+) native resolution
亮度均匀性	>90% for the total screen area
对比度	1500:1 (full white/full black)
灯泡	800 W (Xenon illumination system) <ul style="list-style-type: none">· Typical lifetime: 1700 hours· Maximum lifetime: 2000 hours
数字微镜器件	3 high-resolution SXGA+ active stereo DMD™s
特性	Standard: <ul style="list-style-type: none">· Bi-cubic WARP™· Synchronous and asynchronous active stereo display· DynaColor™/Linked DynaColor™· Stereo-Creator· i-Blend™ (two-or three channel)· economy mode· Shutter Optional: <ul style="list-style-type: none">· Optical Soft Edge Matching (OSEM)· Mono mode· Infitec™ (Switchable)· External polarization (linear or circular)· GISCU™: multi-system and multi-site color management
噪音级别	< 60 dBA at 40°C < 54 dBA at 20°C
兼容性	<ul style="list-style-type: none">· Active stereo capabilities up to SXGA+ at 110Hz· WARP 6™ based pixel map processor using bi-cubic interpolation algorithms for advanced geometry corrections up to a pixelclock of 205 MHz· All current available video sources in RGB or DVI
输入	1 multifunctional 5-cable input (high bandwidth) for connection of: <ul style="list-style-type: none">· RGB analog signals with standard sync (BNC connectors), sync on green or separate sync· 1 Stereo sync input (mini DIN)· 2 stereo outputs (coax)· 1 DVI input
通信	<ul style="list-style-type: none">· RS232 or RS422 loop-through input (D9-connector) for PC-based projector control· Communication input (D9 connector) for peripherals

技术规格**GALAXY 4 LL+**

镜头	Lens type	order nr.	throw ratio
	Fixed lens (Manual focus)		
	TLD (0.8:1) HB*	9842040	0.75
	TLD (1.2:1)	9840770	1.1
	Motorized zoom and focus		
	TLD (1.6-2.0:1) HB*	9842060	1.5 to 1.8
	TLD (2.0-2.8:1) HB*	9842080	1.8 to 2.6
	TLD (2.8-5.0:1) HB*	9842100	2.6 to 4.6
	TLD (5.0-8.0:1) HB*	9842120	4.6 to 7.3
	* High brightness lens		
镜头移动	Motorized V shift: up to 100% Motorized H shift: up to 65%		
功率消耗	1400 Watts		
电源	230V (tolerance 180V -255V)		
环境温度	Max. 35°C		
净重	net weight: 124 lbs/56 kg shipping weight: 210 lbs/95 kg		

生成于: 16 Mar 2023技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。