

D-Cine Premiere DP100

2k Digital Cinema projector for large screens up to 20m (65.6ft)



Technische Daten

D-CINE PREMIERE DP100

Allgemeine technische Daten

Lichtausgabe	22,000 cinema lumens
DMD TM -Chip	3 x 1.2" dark metal type Advanced DLP Cinema TM signal processing: CineCanvas TM image management; CinePalette TM color management, CineBlack TM contrast management and CineLink TM security management
Panel-Auflösung	2048 x 1080
Gehäuse	Hermetically sealed DMD TM and optical assembly
Bildbreite	Screen width (screen gain 1.8) @ 14ftL: 25m -82ft adjustable light output CLO software
Montage	Standing on pedestal, including caster & wheels Up to 15 degrees tilt on pedestal
Lampe	1.5k to 7k Xenon arc lamp sizes Compatible with standard and high performance lamp types
Kontrast	2000:1
Digitale Video-Eingänge	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Primärobjektive	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Projektoriendiagnose	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
Stromversorgungsanforderungen	3 x 400V + N or 3 x 220V version available max. 29,250 BTU/hr (with 6.5kW lamp)
Abmessungen	projector head: 640(H) x 730(W) x 1186(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch projector head + pedestal: 1466(H) x 730(W) x 1252(D) mm / 57.7(H) x 28.7(W) x 49.3(D) inch
Gewicht	projector head + pedestal: approx. 205kg (452lb)
Optionen	- CLO -Constant Light Output control - Anamorphic lens fitting for 1.25:1 scope lens - Acsar 2 Alternative Content Input Processor - ImagePRO HD - SNMP agent (v3)
Bestell-Information	EU: R9010111 US: R9010118

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.