

# FLDX 0.8 - 1.21 : 1 (EN66)

## Short focus



Focus range: 0.7 - 7.0 mThrow ratio

- WUXGA 0.75 - 1.13 : 1
- WQXGA/4K 0.80 - 1.21 : 1
- F80: 1.06 - 1.60 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)
- F400-HR: 0.71 - 1.06 (native 4K) (Requires the use of individual F400-lens adapters)

**Product specificaties****FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS****General specifications**

Platformen	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.06 -1.60 : 1 (WQXGA/4K UHD)
Effectieve f-getal	F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory
Zoomverhouding	1.51 Motorized zoom and focus with memory
Brandpuntsafstand	15.98-23.99 mm
Focusbereik	0.7-7.0 m
Gewicht	3.3 kg
Verzendgewicht	4.0 kg
Projectieverhouding	DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2%

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.

[www.barco.com](http://www.barco.com)

**BARCO**