

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



Focus range: 0.7 - 7.0 m

Throw ratio

- WUXGA 0.75 - 1.13 : 1
- WQXGA/4K 0.80 - 1.21 : 1
- F80: 1.06 - 1.60 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)
- F400-HR: 0.71 - 1.06 (native 4K) (Requires the use of individual F400-lens adapters)

Product specificaties**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS**

General specifications	
Platformen	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.06 -1.60 : 1 (WQXGA/4K UHD)
Effectieve f-getal	F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory
Zoomverhouding	1.51 Motorized zoom and focus with memory
Brandpuntsafstand	15.98-23.99 mm
Focusbereik	0.7-7.0 m
Gewicht	3.3 kg
Verzendgewicht	4.0 kg
Projectieverhouding	DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2%

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.