

LC-3001

30" WQXGA LCD display



Barco's High-Resolution LCD display LC-3001 has been specifically designed for use in a wide variety of professional applications. The LC-3001 presents crisp, clear and color-accurate images on 30" screen size with WQXGA resolution (2560x1600 pixels).

Your benefits:

- High brightness
- High contrast, even in high ambient light environments
- High resolution and pixel density
- Frame lock and genlock functionality
- Low power consumption
- Long lifetime

技术规格

LC-3001

一般规格

技术	TFT LCD
分辨率	2560x1600
寿命	平均 50,000 小时
颜色	16.8 百万
色阶度	76% NTSC
宽高比	16:10:00
视角	176°/176°
响应时间	6 微妙
每英寸点数	101 dpi
颜色调节	6500K
对比度	650:01:00
亮度	250cd/m ²
灯传感器	背光稳定传感器
标准输入	2 路 DVI 输入
支持分辨率	2560x1600
控制	-RS232 control -DDL WMMV -On Screen Display (OSD)
输入	90V-264V (45Hz-65Hz)
功率消耗	150W
工作温度	10°至 40°C (50°至 85°F)
湿度	更大 80%
校准	CE, UL, FCC
冷却方式	低噪声级 21 dB(A) / 无风扇冷却
屏幕对角线距离	29.8 英寸 (756.3 毫米)
可视区域尺寸	641.3 x 400.8 毫米 (25.24 x 15.78 毫米)
尺寸	697 x 456 x 107 毫米 (27.4 x 17.9 x 5.91 英寸)
净重	15 公斤 (33 磅)
遮光玻璃	标配
吊柜	VESA 100 x 100
保修期	产品保修期两年。 图像残留保修期根据特定使用情况而定。

生成于：09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。