

SLM R8 Performer

A Compact Projector for Rental & Staging Applications



Product specificaties**SLM R8 PERFORMER**

General specifications	
Lichtuitvoer	8.000 ANSI Lumen
Digital MicroMirror Device™	3 high resolution SXGA DMD™'s
Resolutie	1280 x 1024 (SXGA)
Helderheidsuniformiteit	> 90 % for the total screen area
Contrast	Normal mode: 800:1 High mode: 1600:1 (Full White/Full Black)
Lamp	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp Power: 2,0 kW
Geluidsniveau (bij 20°C -68°F)	
Geluidsniveau (bij 40°C -104°F)	
Netspanning	200 -240 V
Energieverbruik	2.550 W
Omgevingstemperatuur	35°C (95F) max
Grootte	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Gewicht (inclusief takeluitrusting)	57 kg (126 lbs)
Lenzen	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lensverschuiving	Motorized V shift: up to 100% Motorized H shift: up to 65%
Verzegelde DLP™-kern	No
Naadloos schakelen	Standard
ScenergiX	Standard
Netwerkverbinding	Optional
Vaste ingangen	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or seperate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input)
Optionele ingangen	One free digital input slot for optional input modules: · SDI · HD -SDI
Afstandsbediening	<ul style="list-style-type: none"> • RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.