

DP4K-36BLP

Smart Laser cinema projector for screens between 23-27m (75-89 ft)



- **Reduced total cost of ownership**
- **Unprecedented ease of mind**
- **Superior image quality**

Designed for large to mid-size movie screens, the DP4K-36BLP delivers consistent, razor-sharp, and high-contrast images with native 4K resolution and 35,000 lumens brightness.

Reduced total cost of ownership

Eliminating all lamp-related costs, the DP4K-36BLP provides a very attractive TCO. Thanks to its unique cooling system, the projector boasts a 30,000-hour constant brightness at typical usage conditions. Its significantly higher optical efficiency results in electricity bill savings of up to 40%.

Unprecedented ease of mind

The DP4K-36BLP cuts operating expenses, reduces operational complexity, and optimizes labor cost. It increases your uptime and frees you from all lamp-related costs, administration, and maintenance.

Superior image quality

The DP4K-36BLP offers consistent DCI-compliant image quality with native 4K resolution, outstanding uniformity, and higher contrast on white and silver screens. Its light output can be dimmed to 30% of the initial brightness, enabling 2D and 3D showings from the same projector.

Retrofit ready

If you already own a Barco B-series projector you can replace your current lamp house with the unique laser phosphor retrofit module through an easy on-site upgrade.

Product specificaties**DP4K-36BLP**

General specifications	
Helderheid	35,000 lumens (typical)
Native contrastverhouding	2,000:1 (typical)
Primelenzen	1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 1.95-3.26; 2.53-4.98
Resolutie	4,096 x 2,160
Langdurige stabiliteit van helderheid	30,000 hrs @ average usage conditions
Afmetingen (B x L x H)	Projector: 754 x 1,129 x 604 mm / 29.69 x 44.5 x 23.78 inches Cooler: 561.5 x 738.5 x 348 mm / 22.11 x 29.07 x 13.7 inches
Gewicht	Projector: 143kg (315 lb) Cooler: 32kg (70.6 lb)
Lengte koelvloeistofslang	4 hoses; 0.5m, 2.5m, 5m and 8m (1.6ft/8.2ft/16.4ft/26.2 ft)
Verticale scheiding tussen koeler en projector	Maximum 3m (10ft) (higher or lower)
Voedingsvereisten	Projector: 3x 400V + N or 3x 220V Cooler: obtains power from the projector
Warmtebelasting (max. vermogen)	13023 BTU/h
Omgevingstemperatuur	30°C (86°F) Max. (projector and cooler)
Omgevingsvochtigheid	85% Max. (projector and cooler)
Energieverbruik	Projector (incl. cooler): 4.0 kW
Mediaserver	Barco Alchemy ICMP and other IMB brands supported.
Geluidsniveau	dB(A) @ 1 m: 67.6 dB(A) 62 dB(A) (half fan speed)
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby3D and 6P) are not supported.
Veiligheidsvereisten	Class 1 risk group 3 Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none">▪ workplace safety as prescribed by the local authorities▪ basic laser safety training for operators▪ laser safety program implementation in the company;▪ access limitation only to trained personnel: area labelling, etc.

Laatst bijgewerkt: 17 May 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.