


TF10

10.2mm pixel pitch, 6,500 nits outdoor LED tile for fixed installation



Excellent brightness, color and contrast

The TF10 tiles deliver an excellent balance between brightness, color and contrast. By nature, their low maintenance requirements and proven track record result in an exceptionally low total cost of ownership.

Product specificaties	TF10
General specifications	
Pixelpitch	10.2 mm
Helderheid	6,500 nits
Led-configuratie	3-in-1 SMD
Pixeldichtheid	9,612/sqm 893/sqf 5,768/tile (80x72)
Hor. kijkhoek	140°
Vert. kijkhoek	-35°/+10°
Energieverbruik	184W/m ² (average) 633W/m ² (max.)
Warmtedissipatie	627 BTU/hr/m ² (average)
Paneelafmetingen	Width: 816mm Height: 735mm Depth: 231mm
Gewicht / tegel	31 kg (68.4 lbs)
IP-classificatie	IP65/54
Verwerking	16 bit/color
Onderhoudsgemak	Front and back
Bedrijfstemperatuur	-20 to +50°C (-4° to 122°F)
Operationele vochtigheid	10-99%
Certificeringen	ETL, CE, FCC Class A, RoHS

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

