

S3-4K Jr

Compact and cost-effective Event Master processor



- **Easy and reliable show setup and production**

- **Market-valued 4K performance**

- **Future-proof upgradability to the full S3-4K system**

Powerful features, easy operation

- Modular card-based design
- Easy set-up with the cross-platform Event Master Toolset, providing a step-by-step approach to system configuration
- Serviceable in the field and ready for future signal interfaces via the modular Event Master cards
- Dual, redundant power supplies for maximum peace of mind (optional)
- Widescreen blending support

Product specificaties

S3-4K JR

General specifications

Model	NGS-3U
Live-effectencanvas	10 Megapixels PVW/PGM 20 Megapixels PGM only
Video-ingangen	8 HD inputs via 2 input cards (Event Master series cards) <ul style="list-style-type: none">Up to 2x 4K inputs - each input card supports up to 4K@60p4x SD/HD/3G SDI2x HDMI 1.4a (297 MHz)2x DisplayPort 1.1 (300 MHz)
Video-uitgangen	8 HD outputs via 2 output cards (Event Master Series Cards) <ul style="list-style-type: none">Up to 1x 4K outputs - each output card supports up to 4K@60 p4x HDMI 1.4a (297 MHz)2x HDMI 1.4a for Multiviewer (297 MHz max) or 4x HDMI 1.4a when used as standard output card
Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
Programma-uitvoer	4 program outputs configurable as single screens or tiled/blended widescreens Configurable from 4x 2048x1200@60 max to 1x 4096x2400@60 max Independent edge blending/feathering control for all four sides
Aux-uitgangen met schaalverdeling	User-definable from 4x 2048x1200@60 to 1x 4K@60 All outputs can be defined as Aux destinations for a total of 8 Aux outputs Output color correction
Mixers	<ul style="list-style-type: none">Native resolution background mixer per output screenIndependent layer transitions or full Preview/Program transitionFlexible layer allocation – 2 mixable or 4 single scalable PIP/key layers assignable to any Program output screen
Geheugenruimte voor foto's	Up to 100 HD or 25 UHD, depending on the import file size.
Laageffecten	<ul style="list-style-type: none">Borders (hard, soft, halo) and drop shadowsColor effectsStrobe, H&V flipLuma, chroma and Cut/Fill keys (not all modes support keying)PIP moves via Keyframes
Multiviewer	<ul style="list-style-type: none">Flexible user-definable layoutsMonitor all Inputs and Outputs, including Preview and AuxTwo outputsDedicated hardware same as E2 Event Master Processor
Uitbreidbaarheid	Linking is available as an upgrade option
HDCP	HDCP compliance determined by installed cards
Controle	<ul style="list-style-type: none">Event Master screen management software for PC or MacEvent Master ControllersWebUIEthernet RJ-45, 1000/100/10 Mbps autosense
Onderhoudsgemak	<ul style="list-style-type: none">Field-serviceable I/O and processing cards (not hot-swappable)Hot-swappable dual-redundant power supplies
Geluidsniveau	Max 51.3 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779
Afmetingen	<ul style="list-style-type: none">Height: 13.26 cm / 5.22' 3 RU rack mount unitsWidth: 43.2 cm / 17" without chassis handles, 48.3 cm / 19" with chassis handles attachedDepth: 54 cm / 21.33" overall
Gewicht	21.3 kg / 47 lbs
Vermogen	Input power: 100-240 VAC 50/60Hz 700W Ships with single power supply. Optional Dual-redundant, hot-swappable power supplies available as upgrade.
Omgevingstemperatuur	0-40° C / 32-104 F
Omgevingsvochtigheid	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
Garantie	3 years parts and labor

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.