

CVHD-31B

3,000 lumens, Full HD, single-chip DLP projector



- Razor-sharp images with vibrant colors
- Large lens shift range for flexible installation
- Compact design
- 24/7 reliability

*Only available at selected distributors

The CVHD-31B will perfectly complement your meeting room, conference room or boardroom.

A compact projector

Combining a brightness level of 3,000 lumens with Full HD resolution, the CVHD-31B is a compact projector. Weighing only 2.9 kg, it is lighter than comparable projectors and in size it's more than 25% smaller!

Crisp and vivid images

The CVHD-31B provides razor-sharp, stable and high-contrast images that allows meeting participants to concentrate better and focus longer. It always shows vivid colors, in excellent quality.

Small footprint, ultimate performance

The CVHD-31B features a filter-free design and reliable DLP technology for unmatched picture accuracy and low total cost ownership. Designed for unlimited use, it also comes with a three-year warranty, for true peace of mind.

Product specificaties**CVHD-31B****General specifications**

Technologie	optical lens shift design
Resolutie	1,920 x 1,080 (Full HD)
Helderheid	3,000 ANSI lumens
Type projector	Single-chip DLP projector
Contrastverhouding	2,500 : 1
Helderheidsuniformiteit	>80%
Beeldverhouding	16:9
Type lens	All glass lenses
Lenzen	Standard Zoom lens (1.64-2.06:1)
Optische lensverschuiving	Vertical
Kleurcorrectie	RealColor™
Lampen	220W UHP lamp
Levensduur lamp	Up to 2,250 hours (full power) / 3,000 hours (eco mode)
Lampbehuizing, snelle vervanging	Yes
Lampgarantie	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	Table – ceiling (360 degrees through portrait mode)
3D	No
Ingangen	1 x HDMI (1.3), 1 x DVI-D, 1 x VGA, 1x RCA composite video, 1 x 4-pin mini DIN Y/C, 1 x RCS x3 YUV
Invoerresoluties	1,920 x 1,200 -640 x 480 pixel resolution (model dependent) / RGBHV, RGBS, RGsB
Softwaretools	Projector Toolset
Controle	IR, RS232, Ethernet
Netwerkverbinding	1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 1 x USB
Voedingsvereisten	3.0-1.3A, ~100-240V, 50-60Hz
Energieverbruik	Max 290W
Geluidsniveau	30 dB
Operationele omgevingstemperatuur	10 -40 °C (storage temperature: -20 -60 °C)
Vochtigheid in bedrijf	20 -80% RH
Dissipatie BTU	Less than 1,061/hour
Afmetingen (B x L x H)	278 x 234 x 94 mm / 10.94 x 9.21 x 3.70 inches
Gewicht	2.9 kg (6.39 lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A and cCSAus
Garantie	Limited 3 years parts and labor. Extendable up to 5.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO