

BARCOReality 8200



Технические характеристики

BARCOREALITY 8200

Общие характеристики	
Совместимость	All current Video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards (ACTV, IDTV, EDTV, Eureka 95, Hi-Vision, ...) All computer graphics formats from CGA, EGA, VGA, Mac, S-VGA, XGA, S-XGA, up to electronic workstations with a resolution up to 2000 x 1280 pixels (pixel clock up to 200 MHz)
Контрастность	>250:1 (on 5x4 B/W checkerboard) >500:1 (full white/full black)
Светоотдача	2600 Lumen full white 2200 ANSI Lumen
Размер экрана	Min.: 1 m x 0.75 m (3.3' x 2.5') Max.: 15 m x 11.25 m (50' x 37.5')

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.

www.barco.com

