

LC40-M



The LC40 delivers crisp, clear images detailed to perfection. Compatible with a wide variety of signal sources, it is capable of showing analog and digital video as well as data content - scheduled in sequence or picture in picture -, bringing you the ideal medium to display your message to the right audience, at the right time, at the right place.

With optional components that allow you to tailor the display – both in functionality and look & feel - to your specific needs, The LC40 can easily be integrated in any environment. By combining an integrated PC, content management and scheduling software as well as the high-resolution LC40 display, Barco offers you a total solution for dynamic digital signage.

技术规格**LC40-M****一般规格**

技术	TFT LCD
自然分辨率	1280 x 768 (W-XGA)
屏幕对角线距离	1010mm (39.6")
可视区域尺寸	862mm x 517mm (33.9" x 20.4")
水平观察角度	170°
垂直视角	170°
寿命	typical 50,000h
净重	25kg / 55.1lbs
对比度	600:1
亮度	450NIT
颜色	16.8 million
宽高比	15:9
标准输入	DVI, RGBHV (on BNC), SDI
控制	RS232 control On Screen Display (OSD)
电力要求	Input: 85V-264V (50Hz-60Hz)
功率消耗	270W (330W including Compact PC)
操作T°	5°C to 40°C (41°F to 104°F)
湿度	Max. 85%
校准	UL, CE

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。