

iQ Pro R400

Barco's networked LCD projector with SXGA+ resolution and an amazing brightness level of 4,000 ANSI lumens.



Especificações técnicas

IQ PRO R400

Especificações gerais	
Saída de luz	4,000 ANSI lumen
Uniformidade de brilho	>95 % for the total screen
Razão de contraste	>400 : 1 (full white/full black)
Telas de LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3).
Resolução	1366 x 1024 (native)
Rede	<p>iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs</p> <ul style="list-style-type: none">■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...■ RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)■ 4 USB connectors■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Compatibilidade	<p>The iQ Pro R400 is compatible with:</p> <ul style="list-style-type: none">■ All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats■ All currently proposed HDTV, extended and improved television standards (1080i, 720p)■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA■ Most Macintosh computers■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz■ Most computer sources with a pixel clock up to 160 MHz DVI sources up to SXGA
Recursos	<p>· Advanced picture-in-picture · Seamless switching with effects · Standard cable basket · Standard light shutter · Advanced digital zoom</p>
Tamanho da tela	From 1-6 m/3-20 ft.
Entradas	<p>1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)</p>

Especificações técnicas**IQ PRO R400**

Lâmpada	2x 250 Watt UHP lamp, in lamp housing Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode
Lentes	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6, 3.0-6.0 times the screen width
Frequências de Varredura	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Deslocamento de Lente	V shift: -30% +120%
Dimensões (LxPxA)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Peso	Net weight, body only: 12.9kg/28.5 lbs.
Comunicação	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Nível de Ruído	
Energia de CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Consumo de energia	Max 650 Watt
Dissipação de Potência	Max 2219 BTU/h
Comutação sem emendas	Standard

Gerada em: 15 Mar 2023

Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte www.barco.com para as últimas informações.