

# SLM R10 Performer

A Compact Projector for Rental & Staging Applications



**Product specifications****SLM R10 PERFORMER**

General specifications	
Light output	10.000 ANSI Lumen
Digital MicroMirror Device™	3 high resolution SXGA DMD™'s
Resolution	1280 x 1024 (native) 1600 x 1200 (max)
Brightness uniformity	90 %
Contrast	Normal mode: 800 : 1 High mode: 1600 : 1 (Full White/Full Black)
Lamp	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs  Lamp power: 2,2 kW
Noise level (@ 20°C -68°F)	< 56
Noise level (@ 40°C -104°F)	< 58
Mains Voltage	200-240 V
Power consumption	2750 W
Ambient temperature	35°C (95 F)
Size	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Weight (including rigging gear)	57 kg (126 lbs)
Lenses	BARCO's "click-and-play™" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lens Shift	Motorized V shift: up to 100% Motorized H shift: up to 65%
Sealed DLP™ core	No
Seamless Switching	Standard
ScenergiX	Standard
Network connection	Optional
Fixed Inputs	<ul style="list-style-type: none"> <li>· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals</li> <li>· 2 Multistandard DVI</li> <li>· SDI input (Serial Digital Input)</li> </ul>
Optional Inputs	One free digital input slot for optional input modules: <ul style="list-style-type: none"> <li>· SDI</li> <li>· HD -SDI</li> </ul>
Remote control	<ul style="list-style-type: none"> <li>• RS232 or RS422 loop-through input (D9-connector) for PC based projector control</li> <li>• Communication input (D9-connector) for peripherals</li> <li>• 3 pin male XLR connector for wired remote (standard remote)</li> <li>• 3 pin female XLR connector for bi-directional communication (rugged remote)</li> </ul>

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.