

TransForm NDN-215 Pro

Networked Display Node



Barco's TransForm N Networked Display Node is a powerful PC-based networked graphics processor. It is used in the networked visualization environment of a TransForm N system and can display encoded streams coming from the Gbit Ethernet/IP network. H-264, V2D and ProServer represent just the top of a long list of supported codecs and streaming formats. Furthermore, the display controller also has a high-end graphics card to perform the rendering operations as are requested by the TransForm N management clients in the network.

High density content – Large display walls

The NDN-215 Pro Output nodes can display high density content and can drive up to sixteen HD displays with a single node. The unit supports multiple different types of displays including the whole range of Barco display solutions like RPC, LCD & LED. Managed by CMS inside the TransForm N system multiple NDN-215 Pro output nodes can be combined in a wall-cluster to show a composed synchronized picture on display walls of virtually unlimited size. The NDN-215 Pro offers a dedicated sync-cable based full frame-lock synchronization between up to 30 nodes suiting the needs of video-walls with advanced synchronization requirements.

Features:

- 4 DisplayPort 1.2 outputs
- Up to 4K-UHD resolution per output
- Universal IP video streaming decoding
- Most extensive list of supported codecs and formats

- Network-based content synchronization between multiple display nodes driving a single wall
- Frame lock between multiple display nodes
- Redundant network interface
- Silent operation in a compact and flexible form factor
- Mature Barco quality, robust and reliable

Product specificaties

TRANSFORM NDN-215 PRO

General specifications	
Geheugen	8 GB
Harde schijf	128 GB Solid-State Disk SSD
Netwerk	2x 1Gb/s LAN
Grafische kaart	Professional high-performance NVIDIA Quadro-series graphic card
Processor	Intel(R) Core(TM) i7 Quad core 4GHz processor
Uitgang	4x Display Port 1.2 (supporting up to 4x 4K-UHD) 4x DVI-SL via included adapters (supporting up to 4x HD)
Invoer	H.264, MPEG-2/4, V2D, H.263, VNC, Pro-Server (see supported codec list)
Vormgeving	3U ½ 19" Rackmount housing
Afmetingen	133mm x 220mm x 300mm 5.24" x 8.66" x 11.81"
Gewicht	6.1 kg (7.9 kg incl. packaging)
Voeding	100-240V, 5-3A, 50/60Hz
Energieverbruik	Typ. 124W max. 270W
Temperatuurbereik	0° -40°C 32° -104°F
Vochtigheid	Max. 80% (noncondensing)
Hoogte	Up to 5000m (operation)
Geluidsniveau	Max. 35dbA (measured at 1m/32.8ft distance at 22°/72)
Naleving	CE,CB, IEC 609501, ETL, FCC Class A Regulatory Model Id: NGP-210
Bestelgegevens	R9821017B NDN-215 PRO Display Node (US) R9821017F NDN-215 PRO Display Node (EU) R9821017G NDN-215 PRO Display Node (UK) R9821017X NDN-215 PRO Display Node (C13/C14) R9821099 Rackmount Kit for 2x NGP-210 R766042 Pedestal mount kit for NGP-210

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

