

SP-20

20mm LED sports perimeter solution



Product specifications**SP-20****General specifications**

Calibrated Brightness	7,200 nits measured perpendicular to the display
Pixel pitch	20mm
LED configuration	1R,1G,1B (discrete)
LED density	7,500 LEDs / m ²
Hor. viewing angle	120°
Vert. viewing angle	-15°, +40°
Contrast ratio	3,000:1
Color Processing	16-bit
Dimensions	Width: 960mm / tile Height: 960mm / tile Depth: 250mm / tile
Weight	54kg
Power	Average: 120W /tile Maximum: 370W /tile

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.