



V10v

10mm pixel pitch (virtual), 5,500 nits outdoor LED display



The V series LED displays are specifically designed for fixed installations in branding, digital out-of-home (advertising) and sports. They come at an attractive price without compromising on performance and reliability. Building on Barco's experience with high-end LED technology, the V series is supported by the DV-100 image processor with high-class Athena™ scaler for flexible scaling. Next to supporting standard inputs up to (dual) HD-SDI, the V series also supports new standards like 3G SDI, HDMI and DisplayPort.

Easy setup and management

The V series is managed and controlled by the dedicated V series Toolset (VTS), a direct derivative of the first-class Director Toolset. The VTS comes with an intuitive interface for easy display management and offers advanced options such as brightness, gamma and color temperature control and display configuration. The V series are an excellent choice for basic LED display applications.

Ideally suited for outdoor use

The V10v is a tile-based outdoor LED display geared with a 10mm virtual pixel pitch lamp-type LEDs. It is designed for outdoor use and has successfully passed the Barco typhoon test program. The modular V10v is an easy to install and reliable display that offers a high resolution.

Spécifications techniques

V10V

Spécifications générales	
Luminosité	5 500 cd/m²
Type LED	4 lampes (RGBR)
Densité de pixels	2 500/m² 232/pi² 3 072/module
Angle de vision	H : 140 degrés V : +15/+35 degrés
Taux de contraste	2 000:1
Pas de pixels	10 mm virtuel
Durée de vie	50 000 h (avec une luminosité de 50 %)
Consommation électrique	366 W/m² 146 W/m² (type)
Taille de tuile (l x H x P) en mm	1 280 x 960 x 150
Poids	57 kg/module 125,7 livres
Homologation IP	IP65/44
Traitement	16 bits/couleur
Fréquence de rafraichissement	1 200 Hz
Empilement max.	20 modules
Accrochage max.	40 modules
Interfaces/Ports	CAT5
Disponibilité technique	arrière
Compatibilité des sources (avec le numériseur)	DVI-I (CVBS/YC/YUV/DVI), RVB, SDI (HD/SD), HDMI, DisplayPort
Numériseur utilisable	DV-100
Certifications	CE, ETL, CCC, FCC classe A, RoHS, RoHS (Chine), DEEE

Crée le : 08 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.

