

# S70

Stand-alone 70" display for monitoring, control or collaboration with SXGA resolution and multiple input capabilities.



## Specifiche tecniche

## S70

| Specifiche generali         |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Alimentazione CA            | 95-230 VAC $\pm$ 10%, 50-60 Hz                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Uniformità della luminosità | > 95%                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Comunicazione               | <ul style="list-style-type: none"><li>• 2 x D9 connectors for RS232 in/out</li><li>• 1 x D9 connector for Com 800</li><li>• 1 x Mouse Out (DIN 13)</li><li>• 1 x Mini-jack for wired RC</li><li>• 1 x IR receivers</li></ul>                                                                                                                                                                                                                                                                                                                   |
| Compatibilità               | <ul style="list-style-type: none"><li>• All current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, S-VHS, RGB or component forms</li><li>• All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV ...)</li><li>• All computer graphics formats from VGA, SVGA, XGA to SXGA</li><li>• Most Macintosh computers</li><li>• Electronic workstations with a resolution up to 2,000x1,280 pixels at 76 Hz</li><li>• Most sources with a pixel clock up to 200 MHz</li></ul> |
| Contrasto                   | 350:1                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Profondità                  | The unit is 797 mm deep and has a footprint of 603 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Conformità ambientale       | Ambient temperature 0-40°C   30-105°F at max. 80% humidity (non condensing)                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Altezza                     | 1952 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Altezza con rotelle         | 2003 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Ingressi                    | <ul style="list-style-type: none"><li>• 1 x 5 BNC for: RGB, component video, composite video, S-video</li><li>• 1 x S-video (4-pin mini-DIN)</li><li>• 1 x Video (BNC or cinch)</li><li>• 1 x VGA (D15) connector</li><li>• 3 x Stereo audio L/R (cinch)</li></ul> Optional: <ul style="list-style-type: none"><li>• 1 x Serial Digital Input/Output SDI/SDO</li><li>• 1 x IEEE1394 FireWire</li></ul>                                                                                                                                         |
| Lampada                     | 100 Watts perfectly pre-aligned UHP™ lamp with an operation time of 8000 hours                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Pannelli LCD                | 3 active matrix Poly-Silicon LCD panels (1.8" diagonal), with a resolution of 1,280x1,024 at 24 bit/pixel for 16.7 million colors                                                                                                                                                                                                                                                                                                                                                                                                              |
| Emissione luminosa          | Brightness: 110 cd/m <sup>2</sup> or 500 lumens                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Uscite                      | <ul style="list-style-type: none"><li>• 1 x VGA (D15) connector</li><li>• 1 x Stereo audio L/R (cinch)</li><li>• 1 x Trigger Output Mini-jack</li></ul>                                                                                                                                                                                                                                                                                                                                                                                        |
| Consumo energetico          | Typ. 220 Watts                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Comando da remoto           | All controls are accessible through a soft-touch panel or a new user-friendly backlit IR remote control: <ul style="list-style-type: none"><li>• Source switching</li><li>• User settings per source</li><li>• Installation/Service adjustments</li></ul>                                                                                                                                                                                                                                                                                      |
| Frequenze di scansione      | Horizontal: 15 kHz-115 kHz<br>Vertical: 25 Hz-150 Hz                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Dimensioni schermo          | The screen has an all around visibility. It is the Fresnel lens that provides the evenness of image brightness. Two or more S70 displays can be lined up side by side with a seam of less than 2 mm.                                                                                                                                                                                                                                                                                                                                           |
| Larghezza schermo (min/max) | 1360 mm x 1088 mm<br>53.5 in. x 42.8 in.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Caratteristiche speciali    | <ul style="list-style-type: none"><li>• Cabling, operation and servicing (front access)</li><li>• Available on wheels or with adjustable feet</li><li>• In case of adjustable feet, height of support on customer's request</li><li>• Built-in 2x3 Watt stereo audio amplifier</li><li>• Color temperature adjustment (broadcast 3200°K, film 5400°K, video 6500°K, computer 9500°K or custom)</li><li>• Fits through regular doors</li><li>• Autostart function</li></ul>                                                                     |
| Peso                        | total weight 149 kg   348.33 lbs                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Larghezza                   | 1552 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla [www.barco.com](http://www.barco.com) per le specifiche più recenti.