


NGH-002

Display controller for Networked Broadcast Monitoring System



Product specifications

NGH-002

General specifications

General

- Dual Pentium-based Single Board Computer and dual graphical overlay board
- Dual high-performance 48 bit 65 MHz dedicated graphical bus
- Dual LAN interface 10/100 base-T
- Dual RS-232/RS-422
- Dual CD-ROM drive
- Dual PS-2 mouse/keyboard port
- 2 x 4 free slots for input/output board
- Dual digital DVI input for external graphical overlay
- Dual analog black-burst input for genlock
- Dual LTC/VITC input for master clock synchronization

Dimensions

- Number of slots for in and output boards: 2 x 4
- 19" industrial case, height in rack units: 4U
- Width case: 440 mm | 17.32"
- Width: 483 mm | 19"
- Depth case: 540 mm | 21.30"
- Depth handles: 50 mm | 1.90" /Ll>

- Height: 177 mm | 6.97"

Weight

- Base unit: 21 kg | 44 lbs

Mains

- Number of power supplies: 3 (hot-swap, redundant)
 - Number of power-leads: 2
 - Power supply: 100-240 VAC, 50-60 Hz
 - Power consumption (typical): 450W
 - Heat dissipation (typical): 1550 BTU/h
-

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.