

SLM R8 Performer

A Compact Projector for Rental & Staging Applications



技术规格

SLM R8 PERFORMER

一般规格	
光输出	8.000 ANSI Lumen
数字微镜器件	3 high resolution SXGA DMD™s
分辨率	1280 x 1024 (SXGA)
亮度均匀性	> 90 % for the total screen area
对比度	Normal mode: 800:1 High mode: 1600:1 (Full White/Full Black)
灯泡	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp Power: 2,0 kW
噪音级别(@ 20°C -68°F)	
噪音等级 (@ 40°C -104°F)	
电源电压	200 -240 V
功率消耗	2.550 W
环境温度	35°C (95F) max
尺寸	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
重量 (包括装备齿轮)	57 kg (126 lbs)
镜头	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
镜头移动	Motorized V shift: up to 100% Motorized H shift: up to 65%
封装DLP™内核	No
无缝切换	Standard
ScenergiX	Standard
网络连接	Optional
固定输入	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input)
可选输入	One free digital input slot for optional input modules: · SDI · HD-SDI
远程控制	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control · Communication input (D9-connector) for peripherals · 3 pin male XLR connector for wired remote (standard remote) · 3 pin female XLR connector for bi-directional communication (rugged remote)

生成于: 16 Mar 2023

技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。