

# OverView KVL-621

Industry-standard 60" full HD 16:9 LED video wall

24/7  
OPERATION

LOW NOISE

LED  
TECHNOLOGY

full HD  
1920 X 1080



With the OverView KVL series, Barco has launched a display range that has a well balanced set of essential features, perfectly fitting the standard requirements. All this comes without any compromise in quality, and with a special focus on limiting both the initial purchase as the runtime cost.

The OverView KVL-621 is an easy to operate 16:9 LED-lit projection module that has been designed to offer the typical detail, brightness, and features in full HD resolution for demanding small to medium-sized control rooms.

### Unmatched LED lifetime

Barco's unique cooling system significantly reduces the temperature of the LEDs. This not only prolongs the lifetime of the LEDs (>80,000 hrs), but also allows for durably higher brightness levels. The long LED lifetime guarantees a great uptime and very low overhead costs. The latest LED technology ensures that the power consumption is 30% lower than comparable products.

### Comfortable viewing experience

To ensure good wall uniformity in terms of color and brightness levels, the OverView KVL-621 comes with Barco's Sense<sup>5</sup> automatic calibration system. This system works with an advanced color sensor that continuously measures the primary color levels of the entire wall, and adjusts white point and color when needed. This results in a significantly more accurate cube to cube uniformity, over the complete runtime. Furthermore, the module's robust structure makes the OverView KVL-621 suitable for use in industrial environments.

**Key characteristics**

- 6x redundancy of LEDs (per color)
- Sense<sup>5</sup> automatic white point and primary colors calibration, for brightness and color stability
- Unique cooling system ensures longer LED lifetime
- Low power design
- Wide color gamut
- Less disposables, less waste
- 16:9 aspect ratio

**Product specifications****OVERVIEW KVL-621****General specifications**

Resolution	1920x1080
On-screen contrast	1,200,000:1 (dynamic) 1,600:1 (typ)
Screen	WV-FEL
Input voltage	90 – 240 V, 50-60Hz
Signal input/output	Dual link DVI in / Dual link DVI out
Pixel clock	320 MHz
Input frequency	24 – 62 Hz
Genlock	49 – 61 Hz
Third party interface	WEB service API (optional)
Display technology	DLP rear projection
Screen gap	< 1 mm   0.04" (@25°C) < 0.2 mm   0.0079" (at higher temperatures)
White point	6500K, 3200K fix
Brightness	on-screen: 320 Cd/m <sup>2</sup>
Brightness uniformity	>95%
Color stability	Self calibration with Sense5 based on advanced color sensor
Light source	Light source 6x redundancy for each of 3 LEDs
Light source lifetime	> 60,000h (typ.) > 80,000h (eco) MTBF LED: > 500,000h
Power	90W (eco) 150W (typ.) 180W (max)
Conditions for operation	10°C-40°C, 80% humidity (nc)
Heat dissipation	310 BTU/h (eco) 510 BTU/h (typ.) 610 BTU/h (max)
Signal processing	Loop through up to 10 cubes Cropping / upscaling
Color gamut	EBU
Direct ethernet access	Built-in web server
Graphical user interface	All settings and operational parameters
Dimensions	<ul style="list-style-type: none"><li>■ Diagonal: 60"</li><li>■ Width: 1328 mm   52"</li><li>■ Height: 747 mm   29"</li><li>■ Depth: 1056 mm   42"</li><li>■ Weight: 106.5 kg   234.8 lbs</li></ul>
Warranty	2 years

**Last updated: 03 Feb 2025**

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.