

iq G200L



技术规格

IQ G200L

一般规格

光输出	2,000 ANSI lumen
亮度均匀性	Brightness uniformity: >95 % for the total screen
液晶面板	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
分辨率	1024 x 768 (native)
灯泡	2x 120 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.
镜头	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6,3.0-6.0 times the screen width
屏幕尺寸	From 1-6 m/3-20 ft.
对比度	>400 : 1 (full white/full black)
扫描频率	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
特性	<ul style="list-style-type: none">· Advanced picture-in-picture· Seamless switching with effects· Standard cable basket· Standard light shutter· Advanced digital zoom
兼容性	The iQ G200L is compatible with: <ul style="list-style-type: none">· All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats· All currently proposed HDTV, extended and improved television standards (1080i, 720p)· All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA· Most Macintosh computers· Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz· Most computer sources with a pixel clock up to 160 MHz· DVI sources up to SXGA
输入	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
尺寸(宽x长x高)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
通信	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
噪音级别	
电源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
功率消耗	Max 350 Watt
功率消耗	Max 1195 BTU/h
安全级别	Compliant with UL1950 and EN60950
电磁干扰	BARCO's iQ G200L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
净重	Net weight: Body only 12.9 kg / 28.5 lbs. Shipping weight: <ul style="list-style-type: none">· without lens max.17.5 kg / 38.5 lbs.· with lens: max.20 kg / 44 lbs.
镜头移动	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
无缝切换	Standard
网络连接	Refer to iQ Pro G200L

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。