

BARCOReality 8200



技术规格

BARCOREALITY 8200

一般规格

兼容性	All current Video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards (ACTV, IDTV, EDTV, Eureka 95, Hi-Vision, ...) All computer graphics formats from CGA, EGA, VGA, Mac, S-VGA, XGA, S-XGA, up to electronic workstations with a resolution up to 2000 x 1280 pixels (pixel clock up to 200 MHz)
对比度	>250:1 (on 5x4 B/W checkerboard) >500:1 (full white/full black)
光输出	2600 Lumen full white 2200 ANSI Lumen
屏幕尺寸	Min.: 1 m x 0.75 m (3.3' x 2.5') Max.: 15 m x 11.25 m (50' x 37.5')

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。