

VSE 40



- 19" rack mountable
- Remote controllable through IR remote from BARCO projector or through RS 232
- Possibility to switch up to 6 inputs
- Video Enhancing : adjustments of hue, saturation, sharpness
- Automatic 75 Ohm termination
- Built-in DVD/VCR tape Video Enhancer
- Full Image Freeze
- Phase Locked Loop Circuit stabilizes the image
- Motion Picture Detection and Processing
- Compatible with all sources ranging from standard television, VCR and DSS to LaserDisc and DVD players