

E2 Tri-combo

Full sized 4K60p Event Master processor



- Full show control with pre-configured cards
- Native 4K60p input and output on a single cable
- Intuitive user interface

The Tri-combo configuration of the E2 features four Tri-combo input cards, and one Tri-combo output card. These new cards support 4K 60p on a single cable. With software version 6.0 and greater, the input cards support 2x 4K60p on a single cable or 6x HD inputs (when installed in dual capacity input slots). The Tri-combo output card supports 2x 4K 60p or 6x HD. This boosts the Tri-combo E2 configuration to an impressive 40 HD inputs or 12 4K60p inputs and up to 5 4K60p or 18 HD outputs. This new E2 has extra capacity and flexibility to support your growing shows.

Product specifications**E2 TRI-COMBO**

General specifications	
Model	NGS-4U
Live effects canvas	Up to 20 Megapixels PWW/PGM 40 Megapixels PGM only 80 Megapixels @30p and PGM only
Video inputs	<ul style="list-style-type: none">■ 40 inputs via 8 input cards (HDMI/DP combo 4 inputs, Tri-combo 6 inputs per card)■ Up to 12x 4K inputs -(HDMI/DP combo 1x 4K@60p, Tri-Combo 2x 4K@60p per card)■ 16x SDI SD/HD/3G/6G/12G connectors■ 8 x HDMI 1.4a (297 MPix/sec max)■ 4 x HDMI 2.0 (594 MPix/sec max)■ 8 x DisplayPort 1.1 (300 MPix/sec max)■ 4 x DisplayPort 1.2 (600 MPix/sec max)
Video outputs	<ul style="list-style-type: none">■ 18 HD outputs via 4 output cards (Event Master series cards)■ Up to 5x 4K outputs■ HDMI output card supports 1 4K60p or 4 HD. Tri-combo supports 2 4K60p or 6 HD■ TriCombo output card supports 4 x SD/HD/3G/6G/12G 1x HDMI 2.0, and 1x DisplayPort 1.2 connectors■ 8x HDMI 1.4a (297 Mpix/sec max)■ 3x HDMI 1.4a output cards support 4 HDMI connectors each. The top two connectors of the card support up to 297 MPix/sec (2560x1600 typical). The bottom two connectors support 165 MPix/sec (1920x1200 typical).■ The right most HDMI card (slot 14) may also be used as a two output Multi-viewer.
Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
Program output	<ul style="list-style-type: none">■ Up to 18 program outputs configurable as single screens or tiled/blended widescreens (preview and Multi-Viewer not available in all configurations)■ Up to 16x 2048x1200@60p or 4x 3840x2400@60p■ Independent edge blending/feathering control for all four sides■ Tri-combo supports 90degree output rotation
Mixers	<ul style="list-style-type: none">■ Native resolution background mixer per output screen■ Independent layer transitions or full Preview/Program transition■ Flexible layer allocation – up to 16 mixable or 32 single scalable PIP/key layers assignable to Program output screens
Still stores	Up to 100 HD or 25 UHD, depending on the import file size
Layer effects	<ul style="list-style-type: none">■ Borders (hard, soft, halo) and drop shadows■ Color effects■ Strobe, H&V flip■ Luma, chroma and Cut/Fill keys (not all modes support keying)■ PIP moves via Keyframes
Multiviewer	<ul style="list-style-type: none">■ Flexible user-definable layouts■ Monitor all Inputs and Outputs, including Preview and Aux■ Two outputs■ Dedicated hardware same as E2 Event Master Processor

Product specifications

E2 TRI-COMBO

Expandability	<ul style="list-style-type: none">■ Easily expandable for larger display applications via proprietary links■ Link units to increase available Inputs and Outputs for larger tiled/blended widescreen applications■ Expansion via simple linking<ul style="list-style-type: none">● Up to 8 E2 chassis can be linked● 2 linking cables are included with each E2 chassis
HDCP	HDCP compliance determined by installed cards.
Serviceability	<ul style="list-style-type: none">■ Field-Serviceable I/O and processing cards (not hot-swappable)■ Hot swappable dual-redundant power supplies
Noise Level	Max 52.9 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779
Dimensions	Height: 17.8 cm (7.0 in) -4 RU Rack mount Width: 43.2 cm (17.0 in) -without chassis handles, 48.3 cm (19 in) with chassis handles attached Depth: 56.9 cm (22.4 in) from front panel to rear panel, 62.2 cm (24.5 in) overall
Weight	31 kg (68 lbs)
Power	<ul style="list-style-type: none">■ Input power: 100-240 VAC 50/60Hz 826 Watt■ Dual-redundant, hot-swappable power supplies
Warranty	3 years parts and labor
Environmental temperature	0-40° C (32-104° F)
Environmental humidity	0-95% Non-condensing

Last updated: 13 Jun 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.