

PHWU-81B

7,500 ANSI lumens, WUXGA, single-chip DLP projector



- Excellent image quality
- Designed for large-screen projection
- Allows for ClickShare and HDBaseT integration

This product is only available in China and via distribution partners.

Developed for midsize and large-screen projection in meeting rooms and boardrooms, this 7,500 ANSI lumens WUXGA projector is the perfect match for your business.

What you'll love about this projector

- Stylish design that seamlessly blends in with your office interior
- High-quality images with an unmatched level of detail and contrast
- Button-free and cable-free for simple operation and less clutter
- Reliable DLP technology for true ease of mind
- Easily upgradable with future connectivity add-ons
- Low cost of ownership thanks to DLP technology and sealed optics
- Preset image modes that allow for flexible color management
- Intuitive control menu with the most common features at your fingertips
- User-friendly remote control that features just one button

ClickShare InsideSupporting the integration of optional connectivity modules, the Barco Corporate AV projectors are fully future-proof and can easily be upgraded with extra functionalities. Based on Barco's wireless presentation system ClickShare, the 'ClickShare Inside' option can be nicely integrated under

ClickShare Inside Supporting the integration of optional connectivity modules, the Barco Corporate AV projectors are fully future-proof and can easily be upgraded with extra functionalities. Based on Barco's wireless presentation system ClickShare, the 'ClickShare Inside' option can be nicely integrated under the hood of the projector and allows users to wirelessly share their content on-screen, for true collaboration.

ClickShare Inside

Supporting the integration of optional connectivity modules, the Barco Corporate AV projectors are fully future-proof and can easily be upgraded with extra functionalities. Based on Barco's wireless presentation system ClickShare, the 'ClickShare Inside' option can be nicely integrated under the hood of the projector and allows users to wirelessly share their content on-screen, for true collaboration.

Product specificaties**PHWU-81B****General specifications**

Type projector	WUXGA single-chip DLP projector
Technologie	0.67" DMD
Kleurencirkel	4S standard (RGBW)
Resolutie	1,920 x 1,200 WUXGA
Helderheid	7,500 ANSI lumens / 5,450 ANSI lumens (eco-mode)(compliant with ISO 21118)
Contrastverhouding	2,800:1
Beeldverhouding	16:10
ScenergiX	Yes
Type lens	H lens
Lenzen	1.7-2.3:1; 0.8-1.0:1; 1.3-1.8:1; 2.2-2.7:1; 2.8-4.5:1; 4.5-8.7:1
Optische lensverschuiving	Vertical: -0% to +134% / horizontal: -19% to +19%
Kleurcorrectie	Yes
Lampen	2 x 350W AC lamp
Levensduur lamp	Up to 2,000 hours (full power) / Up to 4,000 hours (eco mode)
Verzegelde DLP™-kern	Yes
Optische dowser	Yes
Geavanceerde Picture-in-Picture	Split
Oriëntatie	table -ceiling
WARP	Yes
Geïntegreerde webserver	Yes
Trapeziumcorrectie	Yes
Ingangen	5 BNC (RGBHV, component), S-VIDEO, D-SUB 15-pin, HDMI, DVI-D (HDCP), SDI
Invoerresoluties	up to WUXGA (1,920 x 1,200) 60Hz
Softwaretools	Projector Toolset
Controle	IR, RS232, RJ45
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	100-240V / 50-60Hz
Max. energieverbruik	910W / 690W(eco mode) / 0.3W (standby)
Geluidsniveau (standaard bij 25°C/77°F)	44 dBA (bright mode)/ 39 dBA (eco mode)
Operationele omgevingstemperatuur	5-40°C / 41°-104°F
Operationele vochtigheid	30-90%
Afmetingen (B x L x H)	510 x 660 x 263 mm
Gewicht	21kg
Verzendingsafmetingen (L x B x H)	650 x 840 x 415 mm
Verzendgewicht af fabriek	26.5 kg
Certificeringen	CB test certificate, US emc, US safety, CE emc and safety, CCC emc and safety
Garantie	3 years standard warranty (conditions can differ from region to region. Contact your local sales or service rep for more details)

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com**BARCO**