

BarcoGraphics 6300



- High light output of 2,200 ANSI lumen
- Native panel resolution of 1,024 x 768 pixels
- Vibrant images with remarkable depth and clarity
- Perfect geometry
- Razor sharp in every corner
- Exceptional input compatibility
- Impressive array of input connections
- Easy picture alignment through BARCO's AutoImage feature
- Direct stacking
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement for older generation projectors

Specifiche tecniche**BARCOGRAPHICS 6300****Specifiche generali**

Emissione luminosa	2200 ANSI Lumen
Pannelli LCD	3 active matrix poly-silicon LCD panels (1.8" diagonal) with a resolution of 1,024 x 768 pixels (aspect ratio 4:3)
Compatibilità	All current Video sources in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/60 Hz Most sources with a pixel clock up to 135 MHz
Contrasto	>350:1 (full white/full black)
Lampada	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
Dimensioni schermo	For the zoom lenses : 1 -6 m For the 0.8 lens : 1 -1.7 m
Peso	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 -25 kg / 46.3 -55.1 lbs.

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.