


ILite 8 MD

8mm, indoor, SMD, 1500 Nit, LED display solution



Product specificaties

ILITE 8 MD

General specifications	
Pixelpitch	8 mm
Gekalibreerde helderheid	1500 NIT (calibrated at 6500°K)
Led-configuratie	3-in-1 SMD
Pixeldichtheid	15.680/m² (1.458/ft²) 3.136/tile (56x56)
Hor. kijkhoek	145° + (min. 50% brightness)
Vert. kijkhoek	145° + (min. 50% brightness)
Contrastverhouding	950:1
Levensduur	100.000h (typical use) 45.000h (full white -half brightness)
Energieverbruik	maximum: 400 W/Tile average: 100 W/Tile
Gewicht	13 Kg (28,7 lbs)
Verwerking	+12 bit/color (Color) 8 bit/color (Greyscale)
Kleuren	68,7 billion
Vernieuwingssnelheid	400 Hz (PAL/NTSC minimum)
Temperatuurbereik	operating: 0 -40°C (32 -104°F) storage: -20 -60°C (-4 -140°F)
Vochtigheid	operating: 35 -85% storage: 10 -90%
Broncompatibiliteit	S-Video / Composite / YUV / RGB / SDI / HDSDI / Data DVI up to SXGA
Certificeringen	UL -CE -TUV Class A
Paneelafmetingen	Width: 448mm (17.6") Height: 448mm (17.6") Depth: 127mm (5")

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

