

Barco Orion



The Barco Orion projector brings Barco image quality and craftsmanship home to medium-sized rooms. There are two distinctive optical setups to choose from: the T version is optimized for dedicated home cinemas, delivering perfect Rec. 709 color accuracy; and the M variant is tailored for media rooms where ambient light is not easily controlled. Barco Orion features six interchangeable lens options, and HDBaseT input and its outstanding motorized lens shift ability produce class-leading installation flexibility.

Specifiche tecniche

BARCO ORION

Specifiche generali

Tipo di proiettore	"single chip projector with all glass optical design with replaceable projection lenses and lens shift"
Risoluzione	1920x1080
Emissioni luminosa	1700 and 4000 lumens
Rapporto di contrasto	>2300-5300* : 1 (*w/iris)
Intervallo obiettivo	*0.3 : 1, 0.74 : 1, 0.8-1.08 : 1, 0.92 : 1, 0.86 – 1.16 : 1, 1.06 – 1.62 : 1, 1.6-2.2 : 1, 2.5-3.9 : 1"
Spostamento obiettivo ottico	adjustable: vertical and horizontal, depending on lenses
Lampade	1 x 350W UHP (dimmable)
Durata lampada (tipica)	Up to 2,000 hours (Full power), Up to 2,500 hours (Eco mode)
Trasporto con lampada	yes
Elemento centrale DLP™ sigillato	standard
Compatibilità	"2K/1080i/p, 720p, 576i/p, 480ip, PAL SECAM, NTSC digital and analogue RGB"
3D	"active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models "
Ingressi	"2x DisplayPort 1.2 (HBR2), 1 x DVI-Dual Link, 1 x HDMI 1.4a, 1 x VGA, 2x 3G-SDI, 1x HDBaseT"
Controllo	IR, 1x RS232, 1 x RJ-45 TCP/IP, USB, 2x BNC sync, 1x MiniDIN
Alimentazione CA	100-240V 50-60Hz
Consumo energetico	less than 530W
Intervallo temperature in funzionamento	10 -40 °C /50 -104 °F, 0-3,000m
umidità in funzionamento non condensata	20 -80% RH (Storage Conditions: 10 -90% RH)
Dissipazione BTU	max 1,807 BTU/h
Installazione	table top, ceiling mount, straight down or up.
Dimensioni (PXLXA)	342 x 306 x 143 mm / 13.46 x 12.05 x 5.63 in
Peso	7.5 kg / 16.5 lbs
Colore alloggiamento	black and white
Certificazioni	Compliant with FCC, part 15 Class A and CCC, cCSAus, cUL, UL and CE
Garanzia	Limited 3 years parts and labour

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.