

Barco Orion



The Barco Orion projector brings Barco image quality and craftsmanship home to medium-sized rooms.

There are two distinctive optical setups to choose from: the T version is optimized for dedicated home cinemas, delivering perfect Rec.709 color accuracy; and the M variant is tailored for media rooms where ambient light is not easily controlled.

Barco Orion features six interchangeable lens options, and HDBaseT input and its outstanding motorized lens shift ability produce class-leading installation flexibility.

技术规格

BARCO ORION

一般规格

投影机类型	"single chip projector with all glass optical design with replaceable projection lenses and lens shift"
分辨率	1920x1080
光输出	1700 and 4000 lumens
对比度	>2300-5300* : 1 (*w/iris)
透镜范围	"0.3 : 1, 0.74 : 1, 0.8-1.08 : 1, 0.92 : 1, 0.86 - 1.16 : 1, 1.06 - 1.62 : 1, 1.6-2.2 : 1, 2.5-3.9 : 1"
光学镜片移动	adjustable: vertical and horizontal, depending on lenses
灯	1 x 350W UHP (dimnable)
灯泡寿命 (典型)	Up to 2,000 hours (Full power), Up to 2,500 hours (Eco mode)
可带灯运输	yes
封装DLP™内核	standard
兼容性	"2K/1080i/p, 720p, 576i/p, 480i/p, PAL SECAM, NTSC digital and analogue RGB"
3D	"active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models "
输入	"2x DisplayPort 1.2 (HBR2), 1 x DVI-Dual Link, 1 x HDMI 1.4a, 1 x VGA, 2x 3G-SDI, 1x HDBaseT"
控制	IR, 1x RS232, 1 x RJ-45 TCP/IP, USBA, 2x BNC sync, 1x MiniDIN
电源	100-240V 50-60Hz
功率消耗	less than 530W
工作温度	10 -40 °C /50 -104 °F, 0-3,000m
操作湿度 无冷凝	20 -80% RH (Storage Conditions: 10 -90% RH)
消散 BTU	max 1,807 BTU/h
安装	table top, ceiling mount, straight down or up.
尺寸(宽x长x高)	342 x 306 x 143 mm / 13.46 x 12.05 x 5.63 in
净重	7.5 kg / 16.5 lbs
机箱颜色	black and white
认证	Compliant with FCC, part 15 Class A and CCC, cCSAus, cUL, UL and CE
保修期	Limited 3 years parts and labour

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。