

Barco Kroma MKII



Featuring our 2nd generation LED illumination system, Barco Kroma MKII produces a stunning, wide and extremely consistent color gamut and a rich, vibrant color rendition. With an unmatched 100,000 hour life expectancy, 13 lens options and close to unlimited installation flexibility, Barco Kroma MKII delivers the ultimate in image quality for smaller dedicated home cinema rooms.

Specifiche tecniche

BARCO KROMA MKII

Specifiche generali	
Tipo di proiettore	2nd Generation Solid State LED DLP® projector.
Emissione luminosa	up to 900 lumens
Rapporto di contrasto	Up to 8,000 : 1 (Infinite contrast and total black with Dynamic Black enabled)
Intervallo obiettivo	0.61, 0.75-1.13, 1.12-1.58, 1.58-2.33, 2.37-3.79, 3.8-6.5 : 1
Spostamento obiettivo ottico	adjustable: vertical and horizontal, depending on lenses
Lampade	LED
Durata lampada (tipica)	LED Up to 100.000 hours
Elemento centrale DLP™ sigillato	standard
Compatibilità	*HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i), NTSC, PAL, SECAM, progressive scan*
3D	*active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models, DLPLink™
Ingressi	*2 x DVI-I, 2 x HDMI 1.3a, 2 x VGA 1 x Component, 1 x S-video*
Controllo	*1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x 12V programmable trigger (3.5mm mini jack), 1 x Wired Remote 3.5mm mini jack, 2 x USB AMX Device Discovery, Crestron Certified Partner*
Alimentazione CA	6.5A, 200-240V, 50-60Hz
Consumo energetico	*Certified rating: 8.4A, ~100-240V, 50-60Hz Typical consumption: Max 325W@100V, ~2.7A, 50Hz; ~1.2A, 240V, 50Hz*
Intervallo temperature in funzionamento	10 -40 °C
umidità in funzionamento non condensata	20 -80% RH
Dissipazione BTU	less than 1,100
Installazione	table top, ceiling mount, straight down or up.
Dimensioni (PXLXA)	510 x 376 x 223 mm excluding lens
Peso	12.7 kg, shipping weight 20 kg
Dimensioni con imballo	780 x 520 x 370 mm (WxHxD)
Colore alloggiamento	black and white
Certificazioni	CCC, cCSAus, FCC Class A, cUL, UL and CE
Garanzia	*limited 3 years warranty. Up to five years extended warranty available. Conditions apply.*

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.

