

SLite 14

14mm, IP65 rated LED solution for outdoor LED display installations with long viewing distances.



Product specificaties

SLITE 14

General specifications	
Visuele resolutie	14 mm
Fysieke resolutie	28,0 mm
Gekalibreerde helderheid	5000 NIT (calibrated @ 6500°K +/-10%)
Led-configuratie	2R, 2G, 1B
Pixeldichtheid	5.098/m² (474/ft²) 3.072/panel
Hor. kijkhoek	120° (min.50% brightness)
Vert. kijkhoek	60° (min.50% brightness)
Contrastverhouding	1950:1 (at 200 lux)
Levensduur	50 000 h (full white -half brightness)
Energieverbruik	maximum: 720 W / Tile average: 180 W / Tile
Gewicht / tegel	38.4Kg (84.9lbs) (excluding structure)
Verwerking	color : 14 bit greyscale: 10 bit/color
Kleuren	4.4 trillion
Vernieuwingssnelheid	800 Hz minimum (PAL / NTSC)
Temperatuurbereik	operating : -20°C -40°C (-4 -104°F) storage : -20°C -60°C (-4 -140°F)
Vochtigheid	operating: 10 -99% storage: 10 -99%
D320-invoercompatibiliteit	S-Video -Composite -YUV -RGB -SDI -HDS DI -Data DVI up to UXGA
Certificeringen	ETL -CE – CEBEC -TUV -FCC class A
Paneelafmetingen	width: 896mm (35.3") height: 672mm (26.5") depth: 240mm (9.4")

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

