

OpSpace OpS-110

Small form factor thin client for HD displays



Barco's OPS-110 thin client is a small form factor display controller specifically built to drive up to two displays in HD resolution (1920 x 1080). It is used in Barco OpSpace networked visualization and collaboration environments to display encoded streams coming from an IP network. It supports standard H.264, Barco's low-latency Video2Data (V2D), Virtual Network Computing (VNC) and Remote Display Protocol (RDP) decoding.

Low noise thin client for up to two displays

The OPS-110 is designed and fully qualified for Barco OpSpace environments. Once connected to an OpSpace server, the pre-configured appliance enables customers to capture networked source information from anywhere. It displays these sources with a user-friendly user interface.

Multiple appliances can be combined to show sources as part of a composed desktop on monitors of an OpSpace workstation, a truly unified workspace for mission-critical applications.

This thin client can process up to eight HD-quality sources and allows organizing visual and interactive content as a smart multi-viewer to enhance knowledge and improve decision-making.

Features

- Pre-configured thin client for Barco OpSpace systems
- Linux based OpSpace operating system
- Intel® i7 Quad Core™ processor for low-latency application processing and software based media decoding

- Drives up to two displays in HD resolution (1920 x 1080)
- Processes up to eight HD sources
- Universal IP streaming video decoding (H.264, V2D, VNC, RDP)
- Silent operation
- Small form factor
- Flexible mounting options

Product specificaties**OPSPACE OPS-110**

General specifications		
Platformen	OpS-110	
Geheugen	8 GB RAM	
Netwerk	2x 1Gb/s LAN	
Processor	Intel(R) Core(TM) i7 Quad core CPU 3.4GHz	
Harde schijf	128 GB SSD	
Grafische kaart	Intel HD Graphics 630	
Uitgang	Up to 2x displays HD 1920x1200 @60Hz via DisplayPort (HDMI via included adapters)	
Invoer	IP video sources (H.264), Video2Data (Barco V2D), Virtual Network Computing (VNC), Remote Desktop Protocol (RDP)	
Vormgeving		
Afmetingen	60 x 190 x 190 mm 2.36 x 7.48 x 7.48 in Packed: 230 x 260 x 308 mm 9.06 x 10.24 x 12.13 in	
Voeding	External PSU 150W / 90 – 264 VAC / 47 – 63 Hz	
Energieverbruik	Typ. 83W max. 110W	
Gewicht	2.2kg 4.85 lbs Packed: 4.5kg 9.92 lbs	
Temperatuurbereik	0° -40° C 32° -104° F	
Vochtigheid	Max. 80% (non-condensing)	
Geluidsniveau	Max. 32dbA (measured at 1m/32.8ft distance at 22°C/72°F)	
Naleving	CE, CB, UL, RCM, BIS, CU-EAC, FCC Class A CCC contact Barco Sales	
MTBF	50,000 h	
Montage	Order no.	
	R9811098	P110 VESA Mount (for 1x OPS-110 + 1x PSU)
	R9811099	P110 Rack Mount (for 2x OPS-110 + 2x PSU)

Laatst bijgewerkt: 17 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.