

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.
- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Especificações técnicas**SLM G5 PERFORMER**

Especificações gerais	
Saída de luz	5.000 ANSI lumens
Resolução	1024 x 786 (native) 1600 x 1200 (max)
Resolução	1024 x 786 (native) 1600 x 1200 (max)
Dispositivo de Micro-espelhos Digital (Digital MicroMirror Device™)	3 high resolution XGA DMD's
Uniformidade de brilho	> 90% for the total screen area
Contraste	500:1 (full white/full black) 500:1 (full white/full black)
Lâmpada	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Nível de ruído (a 20 °C (68 °F))	< 43
Nível de ruído (a 40 °C (104 °F))	< 50
Tensão dos Cabos Elétricos	110/230 V
Consumo de energia	1.600 W
Temperatura Ambiente	40°C (104F) max
Tamanho	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Peso (incluindo equipamento de estaiamento)	56 kg / 124 lbs
Lentes	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Deslocamento de Lente	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Núcleo DLP™ vedado	Yes
Comutação sem emendas	Standard
ScenergiX	Standard
Entradas Fixas	• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals • 2 Multistandard DVI • SDI input (Serial Digital Input)
Entradas Opcionais	One free digital input slot for optional input modules: • SDI • HD -SDI
Controle Remoto	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

Gerada em: 16 Mar 2023Especificações técnicas estão sujeitas a alterações sem aviso prévio. Consulte www.barco.com para as últimas informações.