

SLM R9+ Performer

Compact, SXGA+ resolution and 9000 Ansi Lumen light-output.



Especificaciones del producto

SLM R9+ PERFORMER

Especificaciones generales

Salida de luz	9000 ANSI Lumens 9500 Center Lumens	
resolución	1400 x 1050 (native)	
brillo uniforme	> 90% for the total screen	
relación de contraste	1600 : 1 (full field) High contrast mode: 2000 : 1	
pantalla	3 Chip DLP SXGA+ (resolution of 1400 x 1050 pixels (aspect ratio 4:3)).	
características	■ Picture in picture ■ Seamless switching with effects ■ Standard light shutter ■ Rigging point ■ Carrying handle ■ High contrast mode ■ P7 color processin	
Imagen dentro de la imagen	2 sources simultaneous	
entradas	Fixed inputs ■ 2x Configurable 5-Wire (BNC; incl. 2 video decoders) ■ 2x DVI (Digital Visual Interface) Modular inputs Standard: ■ 1x SDI (+ loop through) Optional: ■ 1x HDSDI (+ loop through)	
salidas	DVI out (1400 x 1050) of full screen composed image	
comunicación	■ 1x RS-232C IN (D-9 connector) ■ 1x RS-232C OUT (D-9 connector) ■ 1x RS-232C IN (XLR connector) ■ 1x 2way prop. protocol to Rugged remote (5 pins XLR connector) ■ 1x prop. protocol (RJ45 connector) ■ mini-jack for wired remote control	
compatibilidad	· All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats · All currently proposed HDTV, extended and improved television standards (1080i, 720p) · All computer graphics formats from VGA, SVGA, XGA, SXGA, full HD to UXGA · Most Macintosh computers · Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz · Most computer sources with a pixel clock up to 200 MHz · DVI sources up to SXGA+	
Compatibilidad de fuentes de entrada	max. input: up to 1920 x 1080 and 1600 x 1200	
tamaño de pantalla	From 1-8m / 3-26ft recommended	
frecuencias de barrido	Pixel clock >162Mhz (UXGA 60hz)	
conexión de red	Optional (10 base-T)	
Servidor para el visual integrado	Optional DIMM PC available Remote control projector over ethernet via webserver	
temperatura ambiente	Max 35°C (95°F)	
lámpara	1.75 kW Xenon Warranty univeral lamphouse: 1000 Hrs	
lentes	Lens	Order nr
	TLD (HB) 0.8	R9842040
	TLD (HB) 1.2	R9840770
	TLD (HB) 1.6 - 2.0	R9842060
	TLD (HB) 2.0 - 2.8	R9842080
	TLD (HB) 2.8 - 5.0	R9842100
	TLD (HB) 5.0 - 8.0	R9842120
desplazamiento de lente	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)	
Codificadores de lentes	On zoom and focus (with TLD lenses)	

Especificaciones del producto

SLM R9+ PERFORMER

ratio de desplazamiento	Lens	Throw ratio
	TLD (HB) 0.8	0.75
	TLD (HB) 1.2	1.1
	TLD (HB) 1.6 - 2.0	1.45 - 1.85
	TLD (HB) 2.0 - 2.8	1.85 - 2.55
	TLD (HB) 2.8 - 5.0	2.55 - 4.55
	TLD (HB) 5.0 - 8.0	4.55 - 7.3
	TLD+ (HB) 7.5 - 11.2	7.5 - 11.2
ScenergiX	Standard horizontal and vertical electronic edge blending	
núcleo DLP? estanco	Standard	
Filtros de polvo	Dense, high quality microfilters available as spare kit, in a 6-pack & 24-pack	
nivel de ruido	61 dBA (at 40°C)	
Tensión de red	200-240 V	
consumo de potencia	2250 W	
disipación de potencia	Max 6830 BTU/h	
corriente alterna	190V -255V (50Hz -60Hz)	
peso	56 kg (124 lbs)	
dimensiones	WxLxH 585 x 876 x 429 mm (23.0 x 34.5 x 19.9 inch)	
regulación de seguridad	Compliant with UL1950 and EN60950	
interferencia electromagnética	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A	
información de pedido	Projector: R9010320 Spare lamp: R9841810 6-pack dust filters: R8454096K 24-pack dust filters: R84540924K	

Generado en: 09 Jul 2024

© 2024 Barco nv. Todos los derechos reservados. Prohibida la reproducción total o parcial sin autorización por escrito. Todos los nombres de marcas y de productos son marcas comerciales, marcas comerciales registradas o nombres comerciales de sus respectivos titulares. Debido a la innovación continua, la información y las especificaciones técnicas están sujetas a cambios sin previa notificación. Consulta www.barco.com para ver las especificaciones más recientes.

