

iCon H600

Network-centric, 1080p HD, 6,000 lumens LCD projector



Technische Daten

ICON H600

Allgemeine technische Daten

Lichtausgabe	6000 ANSI lumens
Auflösung	HD 1080 (1920x1080px)
Helligkeitsgleichförmigkeit	> 95 % for the total screen
Kontrast	> 800:1 (full white/full black)
Display	3 x 1.65" polysilicon LCD panel with native HDTV resolution (1920 x 1080 pixels)
Merkmale	■ AutoImage ■ Advanced picture-in-picture ■ Standard cable basket ■ Advanced digital zoom ■ Advanced Desktopintegration
Bild-im-Bild	Background desktop image + up to 4 sources simultaneously (data or video)
Eingänge	Standard: ■ Layer 1: RGBHV or Component input; Composite video input; S-Video input ■ Layer 2: RGBHV or Component input; Composite video input; S-Video input ■ Layer 3: DVI input and D15 input ■ Layer 4: Available for optional inputs Optional: The following input boards can be placed on any of the 4 layers: ■ RGBHV or Component input; Composite video input; S-Video input ■ DVI input and D15 input ■ SDI and HDSDI input and loop trough
Ausgänge	DVI out (1920 x 1080 at 60 Hz) of full screen composed image (including window inserts)
Kommunikation	■ 1x RS-232C (D-9 connector) ■ mini-jack for wired remote control
Kompatibilität	■ All current video sources ■ All current HDTV sources ■ All computer graphics sources with a pixel clock up to 275 Mhz (VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536) ■ DVI up to UXGA and HDTV resolution ■ HD-SDI, SDI optionally available
Eingangsquellenkompatibilität	2048 x 1536 @ 56Hz max input
Bildgröße	From 1-6m / 3-20ft
Frequenzen	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
Netzwerk-Verbindung	2 x 10/100/1000 Base-T Ethernet
Onboard-Display-Server	■ Provides native 1920 x 1080 resolution ■ Pentium 4 2.6 Ghz, 1 Gigabyte DDR RAM, 40 Gigabyte harddisk (upgradeable) ■ 2 x PCMCIA slot for Wireless LAN cards, memory cards, extensions for inputs and outputs, Bluetooth ■ 2 USB connectors and PS2 connector ■ 2 x 10/100 Mb/s Ethernet RJ 45 connector ■ 1x RS-232C (D-9 connector) ■ Included software:
Umgebungstemperatur	5°C up to 40°C
Lampe	2 x 300 Watt UHP lamp Lifetime: 1500 h/lamp
Optiken	■ Fixed lenses: -OGD (0.86:1) R9840491 -OFD (1.27:1) R9840400 -OFD (2.5:1) R9840290 -OFD (7.0:1) R9840410 ■ Zoom lenses: -OHD (1.4 -2.0:1) R9849930 -OHD (2.1 -3.0:1) R9849810 -OFD (3.4 -4.5:1) R9840060 -OFD (4.5 -6.0:1) R9840100
Lens Shift	Vertical: -120% to +120% Horizontal: -50% to +50%
Staubfilter	Dense High Quality Microfilter (front side removeable)
Geräuschpegel	< 39 dB
Netzspannung	90V-255V
Stromverbrauch	Max. 900 Watt
Wärmeabgabe	Max. 2900 BTU/hour
Stromversorgung	90V-255V (50 Hz -60Hz)
Gewicht	35 kg (77 lbs)
Abmessungen	D x W x H, without cable basket: 679 x 567 x 282 mm (26.73 x 22.32 x 11.10 inch)
Sicherheitsstandards	Compliant with UL1950 and EN60950
Elektromagnetische Interferenz	Compliant with FCC rules & regulations, part 15 Class A, CE EN55022 Class A and CCC

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.