

iCon H400

Network-centric, 1080p HD single-chip DLP projector



技術仕様**ICON H400**

一般仕様	
光出力	4000 ANSI lumens
解像度	1920 x 1080 (native)
輝度均一性	> 95% for the total screen
ランプ	2x 250 Watt P-VIP lamp in lamp housing, pre-aligned for max. light output. Typical lifetime: 1,500 h/lamp
光学部	Sealed optical engine
コントラスト比	> 2000:1 (full white/full black; depending on lens, focus and projector settings)
ディスプレイ	1-chip 0.95" DarkChip3® DLP™ 1080p panel with BrilliantColor™ processing and a native HDTV resolution of 1920 x 1080 pixels, 16:9 aspect ratio
カラーホイール	RGBW
特長	<ul style="list-style-type: none">▪ Advanced picture-in-picture (PiP)▪ Intelligent dual lamp system▪ On board PC with Windows OS for network centric operation▪ Advanced desktop integration (source and PiP handling through Windows OS)▪ Sealed optical engine▪ Standard cable basket
入力	<ul style="list-style-type: none">▪ 1x Component video, RGBHV, RGBS or RGsB (5x BNC)▪ 1x Composite video (BNC)▪ 1x S-video (4-pin mini-DIN)▪ 1x VGA (D15 connector)▪ 2x DVI-D (Digital Visual Interface-Digital)
出力	<ul style="list-style-type: none">▪ 1x DVI-D
互換性	<ul style="list-style-type: none">▪ All current video sources in composite, S-video, component or RGB formats▪ All current HDTV sources (720p, 1080i)▪ All computer graphics sources with a pixel clock up to 270 Mhz (VGA, S-VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536)▪ DVI sources up to UXGA and HDTV resolution▪ Apple Macintosh formats
走査周波数	Horizontal 15kHz -140kHz Vertical 25Hz -150Hz
通信	<ul style="list-style-type: none">▪ 1x D9 connector for RS-232▪ 1x IR remote receiver▪ 4x USB▪ 1x RJ45 ethernet▪ 1x PCMCIA slot (Type II)
対応スクリーンサイズ	From 1.2 -6m / 4 -20ft

技術仕様**ICON H400**

レンズシフト	Max. vertical shift from -25% to +140% (with QCLD 0.85:1 lens: +/-25%)
オンボード・ディスプレイ・サーバー	<ul style="list-style-type: none">■ Pentium M 1.6 GHz processor■ 1 GB RAM■ 40 GB harddisk (5,400 rpm)■ Microsoft™ Windows XP™ Professional Multi-language OS installed■ Barco Server software for network communication between display server and clients■ DropZone software■ Proximity Desktop client software■ Remote Control & Diagnostics software
消費電力	Max. 730 Watt
電源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
適合安全規格	Compliant with ETL60950 and EN60950
電磁干渉	Compliant with FCC rules & regulations, part 15 CE EN55022 Class A and CCC
寸法	Projector body with cable basket: W 415 mm (16.34") x H 195 mm (7.68") x D 565 mm (22.24") Without cable basket: D = 487 mm (19.17") Including lens: Dmax = 590 mm (23.23")
重量	Net weight, body only: 16 kg (35.3 lbs) Shipping weight: max. 20 kg (44.1 lbs)

生成日:15 Mar 2023技術仕様は予告なく変更する場合があります。最新情報については、www.barco.com をご覧ください。