

D-Cine Premiere DP50

The Digital Cinema Experience



Product specificaties**D-CINE PREMIERE DP50**

General specifications	
Digital MicroMirror Device™	3 x high resolution S-XGA DLP Cinema™ DMD™ Dark Metal 3 type
Behuizing	Dust-proof; fitted with a quick-change air inlet filter and incorporating a hermetically sealed optics and DMD assembly
Koeling	Integrated 3 chip liquid cooling system and heat exchanger. Temperature alarms indicate out of range operation and/or shutdown lamp power supply.
Resolutie	1280x1024 per Red, Green and Blue channels; equivalent to 3.9 million pixels.
Contrast	1350:1 (full white / full black)
Kleurverwerking	• Bit depth: 45 bit (15 bit per color) • Color Shades: 35 trillion • Color Gamut: 40% better than HDTV (equivalent to film)
Digitale video-ingang	• 2 x SMPTE 292M inputs, Selectable individually or as a linked pair. • Dual port to support future digital cinema formats • Single port compatible with the formats listed below
Grafische invoer	DFP (Digital Flat Panel) interface, 24 bit RGB, 1280 x 1024, with frequency range 23 -96 Hz DVI standard resolutions (640x480 and 1024x768 and 1280x1024). Also supports non-standard packaging at 10 or 12 bit per color
Bedieningsinterface	RS232/RS422 for RC567 D-Cine Premiere controller and PC set-up software or 100 base T Ethernet.
Beeldcontrole	D-Cine Premiere communication software for projector, lens and source set-up plus display geometry (resizing) and masking (cropping) and color calibration.
Beveiliging	High security image processing card frame equipped with Dallas key and 6 Pin number code protection system. Optional fully integrated video and audio decoder.
Voeding	Digital head, cooling pump and touch screen; Auto ranging 90-240V
Gewicht	Digital head and standard single anamorphic lens holder (excluding lens); 52kg / 115lb
Diagnose	Digital head temperature / fan speed / status/ liquid cooling / electronic power supply. Display; RC567 touch screen panel or via Ethernet.

Product specificaties

D-CINE PREMIERE DP50

Lenzen	Prime All focal lengths covered by a wide range of fixed focal length and zoom lenses. X, Y and Z (focus) adjustment Focus range: +/-10mm from nominal position Shift range: 35% of screen height in all directions Anamorphic Lenses 1.5 (flat) and 1.9 (scope) options X, Y and Z adjustment Lens Mounting Single anamorphic lens mount included; Dual lens mount option.
Lampbehuizing	Type Kinoton, FP50D console Illumination Optional 2kW, 3kW, 5kW, and 7kW Xenon Arc lamp depending on screen size Reflector Standard f2.0 dichroic glass type Power Supply Lamp power supply -EUR version IREM 3-7 kW three phase 360-460V 50 Hz Lamp Power supply -USA version IREM 3-7kW three phase 187-230V 60 Hz Projector control 4 x LED status indicators: OK / Power / Communication and Alarm 4 push button control of digital head modes 4 user definable lamp house or automation controls 4 general purpose relays
Opties	Digital Head • Decoder -Fully integrated, tamper-evident, Qualcomm Image Decoder • CLO -Constant Light Output processing • PC Input -For direct connection of a PC input to the digital head. Dual Anamorphic Lens fitting – for 1.5x and 1.9x lenses Remote Touch Screen Projector Control Highly integrated remote control of the operations of the D-Cine Premiere plus a diagnostics display and automation interface. ACSAR Alternative Content Switcher and Router A powerful scaler and router, designed to convert any analogue or digital signal to the DVI digital input of the D-Cine Premiere digital head.

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.