


Input Controller 16

Input Controller 16



- 16 fully configurable inputs One output 19 inch rack mount Standard equipped with Xlite Toolset, controlling software. Multipurpose device: both Daylight Display and Projection Arrange your sources onto your display through an intuitive interface. Scale and position all sources exactly how you want them. Overlay sources using advanced chroma-keying and alpha blending features. Process video and data in pure quality onto your display. Compatible with all standard image formats.

Specifiche tecniche

INPUT CONTROLLER 16

Specifiche generali

Ingresso	16 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Compatibilità	Barco Daylight Displays Projectors
Uscita	DVI-A, DVI-D, RGB
Controllo	· Scaler 16 input channels [Data-Video] fully scalable to desired output resolution · Z-order Instant modification of Z-order control, for each output window · Window positioning Intuitive positioning interface · Connectors RS 232 [RJ11]
Effetti	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Temperatura in funzionamento	0° <-> 45°
Alimentazione	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Informazioni per ordini	R9851580

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.