


OverView MVL-721

Industry-standard 70" full HD 16:9 LED video wall



- High brightness
- Redundancy of critical components
- Low power consumption
- Remote management
- High reliability
- Sustainable product

The OverView MVL-721 is an easy to operate 16:9 LED-lit projection module that has been designed to offer the typical detail, brightness, and features in full HD resolution for control rooms where space is not a constraint.

This follow-up of the successful OverView MVL-721 Gen1 offers a well-balanced set of essential features, perfectly fitting the standard requirements. All this comes without any compromise in quality, and with a special focus on sustainability – in terms of limited power consumption, long lifetime and ability to upcycle.

Unmatched LED lifetime and brightness

The next-generation LED light source drastically improves the brightness of the MVL-721. With a 55% increase in maximum engine light output compared with the first generation, the MVL-721 can be deployed in virtually all indoor lighting conditions. This impressive increase in brightness is realized with the exact same power needs.

MVL-721 also brings an important step-up in reliability, featuring redundant inputs to ensure a continuous data flow, an optional external power supply with automatic failover, and a light source lifetime of over 100,000 hours.

Easy installation and remote management

Barco's Video wall Manager software makes it a lot easier to install, configure and control the video wall. The cloud-based Video wall Management Suite, on its part, allows remote monitoring, diagnostics and control for Barco video walls. Allowing this kind of remote management from a central location, lowers operational costs and ensures faster and more effective troubleshooting.

Product specificaties**OVERVIEW MVL-721**

General specifications			
Resolutie	Full HD (1920x1080)		
Helderheid	Under native color gamut		
	Mode / Screen type	WV-FEL	FXS
	High brightness	540 cd/m ²	460 cd/m ²
	Normal	360 cd/m ²	305 cd/m ²
	Eco	180 cd/m ²	155 cd/m ²
Contrast op scherm	1,200,000:1 (dynamic)		
Weergavetechnologie	Rear-projection DLP (rear access only)		
Kleurenspectrum	REC709		
Wit punt	Customized white points		
Helderheidsuniformiteit	>95%		
Scherm	Mid Gain Type, 180° viewing angle		
Ruimte tussen schermen	Adjustable up to 0.2 mm depending upon video wall configuration and operating temperature		
Kleurstabiliteit	Sense X: automatic real-time color and brightness calibration		
Afmetingen	<ul style="list-style-type: none"> ■ Diagonal: 70" ■ Width: 1550 mm 61.0" ■ Height: 872 mm 34.3" ■ Depth: 1010 mm 39.8" ■ Weight: 104 kg 228 lbs 		
Lichtbron	6x redundancy for each of 3 LEDs		
Geluidsniveau	Less than 20 dB (measured from 5m in front)		
Levensduur lichtbron	> 100,000h in Eco/Normal mode		
Gebruiksomstandigheden	10°C – 40°C 50°F – 104°F Up to 80% humidity (non-condensing)		
Ingangsspanning	90 – 240 VAC, 50-60Hz		
Vermogen	70W (eco) 100W (typ.) 150W (max)		
Warmtedissipatie	240 BTU/h (eco) 340 BTU/h (typ.) 510 BTU/h (max)		
Signaalingang/-uitgang	2x DP1.2 inputs & 1x output (4K@60Hz) 2x HDMI 2.0 inputs (4K@60Hz) 2x USB ports (only for power) 2x Ethernet ports		
HDCP	v2.2		
Externe voeding	Optional: remote and redundant hot swappable power supply		
Signaalverwerking	Loop through Cropping, scaling with wall configuration		
Directe Ethernet-toegang	Built-in web server		
Grafische gebruikersinterface	All settings and operational parameters		
Interface van derden	WEB service API		
Garantie	2 years		

Laatst bijgewerkt: 12 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.