

OLite 612

多功能室内/户外 SMD LED 投影墙（6000 尼特、12 毫米像素间距）可分解成 48 个离散块，从而创建任何形状或外形的 LED 屏幕。



12mm
PIXEL PITCH

IP65
WATERPROOF



技术规格

OLITE 612

一般规格

像素间距	12.4 mm
亮度	6,000 nits
LED配置	3-in-1 SMD
像素密度	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
像素密度	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
水平观察角度	110° (min 50% brightness)
垂直视角	+40, -50° (min 50% brightness)
对比度	1,150:1 (at 500 lux)
寿命	50,000 hours to 50% of initial brightness
功率消耗	800W/tile (max) -240W average (rental) 400W/tile (max) -120W average (fixed)
操作电压	200-240V / 50-60Hz
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
重量 / 层数	58 kg (rental) 17 kg (fixed)
IP等级	IP65/65
处理	16 bit/color
颜色	281 trillion
刷新率	800Hz
内置底座	Max. 12 tiles high
内置构架	Max. 15 tiles high
连接界面	DVI interface (DVI connector)
更大导线长度	4.5m (with Barco DVI cable)
界面	2x DVI link
更大串联	3 tiles
可维护性	Back
工作温度	-20 -45°C
存储温度	-20 -60°C
工作湿度	10-99%
存储湿度	10-99%
信号源兼容性	CVBS, YC, YUV, RGB, DVI, SDI, HDSDI (DX700: and Dual link DVI, Dual link HDSDI)
可操作数字转换器	DX-700 (with DVI output card), D320, LED-PRO
认证	UL, CE class A, TUV, FCC, ClassA

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。