

# FLDX 1.2 - 1.7 : 1 (EN63)

Focus range: 1.5 - 15.0 m  
Throw ratio <br>WUXGA 1.12-1.58:  
1<br>WQXGA/4K 1.20-1.70:1<br>F80: 1.68 - 2.38 : 1 (WQXGA/4K UHD)  
<br>(F80 requires the FLD/FLD+ lens adapter)



**Product specificaties****FLDX 1.2 - 1.7 : 1 (EN63)**

General specifications	
Type lens	FLDX 0.38 : 1 UST 90°
Effectieve f-getal	2.4
Zoomverhouding	1
Platformen	F35, FL40, F70, F80*, F90 and G100** *For use with F80: Lens requires lens adapter (R98014421) **For use with G100: Lens needs lens adapter (R9802360) and lens support system (R9802365)
Projectieverhouding	DMD chip WUXGA (F35, FL40, F70, F90 and G100): 0.38 : 1 WQXGA (F35, FL40, F70 and F90): 0.41 : 1 WQXGA+ (F80): 0.54 : 1 Image size tolerances +/-2%
Brandpuntsafstand	8.2mm
Focusbereik	Standard 133" – 400" for F80, 200" – 600" for F35, FL40, F70, F90 and G100
Projectieafstand	1.6 -5 m
Gemotoriseerde zoom	N/A
Gemotoriseerde focus	Yes
Gewicht	Net: 6.6 kg Gross: 9.7 kg

Laatst bijgewerkt: 03 Nov 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.